

Universal VESA LCD Monitor Mounting Bracket for 19in Rack or Cabinet

Product ID: RKLCDKBK



The RKLCDKBK Universal VESA LCD Monitor Mounting Bracket for 19in Rack or Cabinet lets you mount almost any retail LCD or Touch screen panel into a server/storage rack/cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The LCD mounting bracket is made of solid cold pressed steel (SPCC), is designed to support 100mm and 75mm VESA mounted LCD panels, and meets ANSI/EIA RS-310-D standards rack mounting. A unique adjustable design enables an LCD panel to be mounted into the cabinet at various depths - allowing the rack/cabinet door to be closed.

The LCD mounting bracket also supports wall-mounted LCD installation, by inverting the adjustable bracket or by adding this bracket to a wall mount bracket or rack, such as the 6U (10 inch) Wallmount Bracket for 19" Rack Equipment (WALLMOUNT6) or 8U Open Frame Wall Mount Equipment Rack (RK812WALLO).

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Ideal for installing a retail LCD monitor into an existing Rack or Cabinet solution
- Installing a touch screen display into a rack or cabinet
- Adding a monitoring display to a security rack or cabinet
- Mounting an LCD monitor or TV to the wall
- Use for uptime/process monitoring with big screens over 19" when mounted outwards

Features

- Adjustable 100mm and 75mm VESA mounting hole pattern for greater compatibility and control
- Meets ANSI/EIA RS-310-D standards
- Adjustable depth between 0 to 3.5 inches
- Constructed from solid steel at 2.0mm thick, this bracket is designed for durability
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	4U
Cable Management	No
Industry Standards	EIA RS310-D

Physical Characteristics

Color	Black
Material	Steel
Internal Width	17.3 in [43.9 cm]
Weight of Product	3.7 lb [1.7 kg]
Maximum Mounting Depth	3.5 in [88.9 mm]
Minimum Mounting Depth	0.0 in [0 mm]

Packaging Information

Package Length	18.6 in [47.2 cm]
Package Width	2.1 in [54 mm]
Package Height	8.7 in [22 cm]
Shipping (Package) Weight	4.3 lb [2.0 kg]



**What's in the
Box**

Included in Package	
	mounting brackets
	LCD bracket
	M5 cage nuts
	M5 screws
	M4 x 10mm LCD mounting screws
	M5 x 10mm bracket screws
	washers
	instruction manual

****Product appearance and specifications are subject to change without notice.***

