

## 2U Hinged Solid Blank Rack Panel

**Product ID:** RKP NLHS2U



The RKP NLHS2U 2U Hinged Solid Blank Rack Panel mounts to a standard 19" 2 or 4-post rack to improve the organization and appearance of your rack, while maintaining easy access and helping to guide airflow. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The hinged blanking panel is reversible, meaning it can be installed to open from either the left or right side for easy access to the inside of your rack, while still covering the unused rack spaces for a professional look.

The filler panel is made of high-quality steel for long-term durability, plus the solid design helps to guide airflow along the back of the rack instead of passing through. For easy installation, this rack panel comes complete with rack installation screws (10-32).

For a vented panel, please see our 2U Hinged & Vented Rack Blank Panel (RKP NLHV2U).

Backed by a StarTech.com 2-year warranty.

## Certifications, Reports and Compatibility

### Applications

- Fill in unused gaps between equipment in server racks and cabinets, while still allowing access to the inside of the rack

### Features

- 2U solid rack panel design

- Sturdy steel construction
- Mounts to standard 19" 2 or 4-post server racks
- Includes rack screws
- Hinged for easy access to rack components
- Reversible - install to open from the left or right side
- TAA compliant for GSA Schedule purchases

---

#### Hardware

Warranty	2 Years
U Height	2U
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front Only)

---

#### Physical Characteristics

Color	Black
Material	Steel
Weight of Product	19.6 oz [554.5 g]

---

#### Packaging Information

Package Length	19.9 in [50.5 cm]
Package Width	3.9 in [100 mm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	23.2 oz [658.6 g]

---

#### What's in the Box

Included in Package	2U Hinged Solid Rack Panel
	5/8" #10-32 UNF Screws
	#10-32 UNF Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

