

Solid Blank Panel with Hinge for Server Racks - 4U

Product ID: RKPNLHS4U



You can improve the appearance and airflow of any standard 19-inch server rack while maintaining easy access to server equipment, using this hinged 4U blanking panel. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The blanking panel creates a clean and professional look by covering empty space and visible cables. Adding blanking panels to your server racks offers a tidier appearance for a more organized server room.

This solid rack-panel features a hinged design that enables you to open it for fast and easy access to your rack-mounted devices. You can quickly open the panel, make your required adjustments and when you're finished, simply close the panel to restore the professional appearance and order of your server room. The panel is reversible, which enables you to install it on the left or the right side of your rack, to best suit your needs. This rack panel also comes complete with rack installation screws and nuts, giving you everything you need to ensure a hassle-free installation.

The blanking panel offers a solid design that helps guide airflow down the back of your rack, rather than passing between occupied spaces. Improved airflow helps ensure your rack-mounted equipment is running at an optimal temperature.

The RKPNLHS4U is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Fill in unused gaps between equipment in server racks and cabinets
- Access your covered rack with an open-and-shut design

- Help guide the airflow along the back of your rack, instead of passing through your equipment

Features

- Easily access rack components by opening the hinged panel
- Create a tidy and professional look by covering unused rack space
- Versatile installation options with a reversible blank panel that can open from the left or the right side
- 4U solid rack-panel design
- Mounts to standard 19" 2 or 4 post racks
- Sturdy steel construction
- Rack screws and nuts included
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	2 Years
U Height	4U
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front Only)

Physical Characteristics

Color	Black
Material	Steel
Product Length	18.4 in [46.8 cm]
Product Width	0.9 in [22 mm]
Product Height	7.0 in [17.8 cm]
Weight of Product	2.2 lb [1.0 kg]

Packaging Information

Package Length	20.9 in [53 cm]
Package Width	7.7 in [19.5 cm]



Package Height 1.7 in [43 mm]

Shipping (Package) Weight 2.6 lb [1.2 kg]

What's in the Box

Included in Package 5/8" #10-32 UNF Screws
#10-32 UNF Cage Nuts
4U Hinged Solid Rack Panel

****Product appearance and specifications are subject to change without notice.***

