

2U Tool-Less Vented Blank Rack Panel

Product ID: RKPNLTL2UV



The RKPNLTL2UV 2U Tool-Less Vented Rack Panel mounts to a standard 19" 2 or 4-post rack to improve the organization and appearance of your rack in seconds. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The blank rack panel offers a tool-less design to save you time through simple installation or removal, with locking pins that secure into place with a quarter-turn. The panel is made of high-quality steel for long-term durability, plus the vented design allows for unobstructed airflow through your rack.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

- Fill in unused gaps between equipment in server racks and cabinets
- Use in rack installations where equipment needs to be changed / shifted often

Features

- 2U vented rack panel design
- Sturdy steel construction
- Mounts to standard 19" 2 or 4-post server racks
- Tool-less install / removal with quarter-turn locking pins

- TAA compliant for GSA Schedule purchases

Hardware

Warranty	2 Years
U Height	2U
Industry Standards	EIA RS310-D
Mounting Options	Front Mount (Front Only)

Physical Characteristics

Color	Black
Material	Steel
Weight of Product	10.9 oz [308.9 g]

Packaging Information

Package Length	21.3 in [54.2 cm]
Package Width	4.1 in [10.3 cm]
Package Height	1.5 in [38 mm]
Shipping (Package) Weight	13.5 oz [383.5 g]

What's in the Box

Included in Package	2U Tool-Less Vented Rack Panel
---------------------	--------------------------------

**Product appearance and specifications are subject to change without notice.*

