

## Rackmount PDU with 8 Outlets and Surge Protection - 1U

Produkt-ID: RKPW081915



This 8-outlet (120V 15A)(12A UL) Rack PDU delivers a cost-effective power distribution solution for your server rack/cabinet. The 1U PDU can be mounted horizontally in any server rack 4in in depth or greater, to provide eight 120V 15A power ports/outlets, and features a rugged steel casing to ensure maximum durability.

The front of the PDU features two LEDs to indicate proper ground and surge detection while enabling you to control the power state with an illuminated power/reset switch.

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in circuit breaker and reset switch, ensuring dependable performance of vital equipment.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- 8 easily accessible power outlets in a compact 1U of rack space
- Localize the power control for all of your connected system

## Merkmale

- **POWER AND CHARGE:** This rack mount power strip provides an additional 8 NEMA 5-15 outlets (120V/15A) and features a 6ft (1,8m) long cord so you can plug your devices in while leaving the rack mobile
- **1U RACK DESIGN:** Compatible with all 19" server racks 4 inches or deeper, this horizontal-mount power distribution unit fits many network racks and has an integrated power cord; ANSI/EIA RS-310-D standard
- **EASY INSTALLATION:** This IT-grade rackmount PDU features a rugged steel chassis, LED indicators for ground and surge protection, and lets you control the power state with power and reset switches
- **PROTECTS YOUR EQUIPMENT:** This rack mountable 8-outlet (120V) power strip features a built-in circuit breaker and reset switch, ensuring a dependable performance of your networking equipment
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this rack PDU is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

|                          |            |
|--------------------------|------------|
| Garantiebestimmungen     | 2 Years    |
| Form Factor              | Horizontal |
| Steckdosenkompatibilität | 8          |
| Einbaufähig              | Ja         |

---

#### Leistung

|                                                       |                               |
|-------------------------------------------------------|-------------------------------|
| Allgemeine Spezifikationen                            | Surge Protection: 1800 Joules |
| Max. Eingangsstrom pro Phase                          | 15A                           |
| Max. Gesamtstromaufnahme pro Phase                    | 15A                           |
| Behördlich herabgesetzter Eingangsstrom (Nordamerika) | 12A                           |
| Nominale Eingangsspannung                             | 120V                          |
| Nominale Ausgangsspannung                             | 120V                          |

|                          |         |
|--------------------------|---------|
| Max.<br>Ausgangsspannung | 125V    |
| Belastbarkeit            | 1800 VA |

---

#### Steckverbinder

|                        |                                   |
|------------------------|-----------------------------------|
| Eingangssteckverbinder | 1 - NEMA 5-15 Strom (Nordamerika) |
| Ausgangssteckverbinder | 8 - NEMA 5-15 Strom (Nordamerika) |

---

#### Anzeiger

|              |            |
|--------------|------------|
| LED-Anzeiger | 1 - Ground |
|              | 1 - Surge  |

---

#### Strom

|                  |        |
|------------------|--------|
| Eingangsspannung | 120 AC |
|------------------|--------|

---

#### Umgebungsbedingungen

|                    |                                |
|--------------------|--------------------------------|
| Betriebstemperatur | -5°C to 45°C (23°F to 113°F)   |
| Lagertemperatur    | -25°C to 65°C (-13°F to 149°F) |
| Feuchtigkeit       | 5% to 95% RH non-condensing    |

---

#### Physische Eigenschaften

|                |                   |
|----------------|-------------------|
| Farbe          | Schwarz           |
| Gehäusotyp     | Stahl             |
| Kabellänge     | 6.0 ft [1.8 m]    |
| Produktlänge   | 19.0 in [48.3 cm] |
| Produktbreite  | 3.8 in [9.6 cm]   |
| Produkthöhe    | 1.7 in [4.3 cm]   |
| Produktgewicht | 4.3 lb [2.0 kg]   |

---

#### Verpackungsinformationen

|            |   |
|------------|---|
| Paketmenge | 1 |
|------------|---|

|                                |                   |
|--------------------------------|-------------------|
| Paketlänge                     | 9.2 in [23.3 cm]  |
| Paketbreite                    | 20.5 in [52.1 cm] |
| Pakethöhe                      | 2.4 in [6.2 cm]   |
| Versandgewicht<br>(Verpackung) | 4.9 lb [2.2 kg]   |

---

#### Verpackungsinhalt

|                    |                                    |
|--------------------|------------------------------------|
| Im Paket enthalten | 1 - 8 Port Power Distribution Unit |
|                    | 4 - M5-Schrauben                   |
|                    | 4 - M5 Käfigmuttern                |
|                    | 1 - Installation Document          |

---

#### Garantieinformationen

|          |         |
|----------|---------|
| Warranty | 2 Jahre |
|----------|---------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.