

Rackmount PDU with 8 Outlets and Surge Protection - 1U

Product ID: RKPW081915



This 8-outlet (120V 15A)(12A UL) Rack PDU delivers a cost-effective power distribution solution for your server rack/cabinet. The 1U PDU can be mounted horizontally in any server rack 4in in depth or greater, to provide eight 120V 15A power ports/outlets, and features a rugged steel casing to ensure maximum durability.

The front of the PDU features two LEDs to indicate proper ground and surge detection while enabling you to control the power state with an illuminated power/reset switch.

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in circuit breaker and reset switch, ensuring dependable performance of vital equipment.

Certifications, Reports and Compatibility



Applications

- 8 easily accessible power outlets in a compact 1U of rack space
- Localize the power control for all of your connected system

Features

- **PROTECTS YOUR EQUIPMENT:** This rack mountable 8-outlet (120V) power strip features a built-in circuit breaker and reset switch, ensuring a dependable performance of your networking equipment

- **EASY INSTALLATION:** This IT-grade rackmount PDU features a rugged steel chassis, LED indicators for ground and surge protection, and lets you control the power state with power and reset switches
- **POWER AND CHARGE:** This rack mount power strip provides an additional 8 NEMA 5-15 outlets (120V/15A) and features a 6ft (1,8m) long cord so you can plug your devices in while leaving the rack mobile
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this rack PDU is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance
- **1U RACK DESIGN:** Compatible with all 19" server racks 4 inches or deeper, this horizontal-mount power distribution unit fits many network racks and has an integrated power cord; ANSI/EIA RS-310-D standard

Hardware

Warranty	2 Years
Form Factor	Horizontal
Number of Power Outlets	8
Rack-Mountable	Yes

Performance

General Specifications	Surge Protection: 1800 Joules
Maximum Total Current	15A
Maximum Total Current Draw per Phase	15A
Regulatory Derated Input Current (North America)	12A
Nominal Input Voltage	120V
Nominal Output Voltage	120V
Maximum Output Voltage	125V
Load Capacity	1800 VA

Connector(s)

Input Connector(s)	1 - NEMA 5-15 Power (North America)
Output Connectors	8 - NEMA 5-15 Power (North America)

Indicators

LED Indicators	1 - Ground
	1 - Surge

Power

Input Voltage	120 AC
---------------	--------

Environmental

Operating Temperature	-5C to 45C (23F to 113F)
Storage Temperature	-25C to 65C (-13F to 149F)
Humidity	0% RH

Physical Characteristics

Color	Black
Material	Steel
Cable Length	6.0 ft [1.8 m]
Product Length	19.0 in [48.3 cm]
Product Width	3.8 in [9.6 cm]
Product Height	1.7 in [4.3 cm]
Weight of Product	4.2 lb [1.9 kg]

Packaging Information

Package Quantity	1
Package Length	20.2 in [51.4 cm]
Package Width	9.1 in [23.2 cm]
Package Height	2.4 in [6.0 cm]
Shipping (Package) Weight	4.7 lb [2.1 kg]

What's in the Box

Included in Package	1 - 8 Port Power Distribution Unit
	1 - Installation Document

**Product appearance and specifications are subject to change without notice.*