

10 Outlet Rack Mount Power Strip 125V/16 Amp - 1U Horizontal 19" Rackmount PDU - NEMA 5-20P Input - 10x NEMA 5-15/20R Outlets - Rack Mount PDU - UL Listed - 8ft Power Cord

Produkt-ID: RKPW101920



This 10-outlet (125V 16A) Rack PDU delivers a power distribution solution for your server rack/cabinet. The business-grade 1U power distribution unit can be mounted horizontally in any 19 inch server rack 4" in depth or greater, to provide ten 125V (16A) power outlets. You can access ten plugs on the front of the horizontal-mount network rack PDU.

Consolidate Power Sources

This power distribution system consolidates your power source and enables you to control all powered devices from one switch. The front of the rackmount power strip features two LEDs that indicate proper ground and surge detection, while enabling you to control the power state with an illuminated power/reset switch. This PDU includes an 8 ft long power cord.

Built to Last

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in 20 Amp (20A) circuit breaker and reset switch, ensuring dependable performance of vital equipment. To ensure maximum durability, the power distribution unit itself features a rugged steel casing.

This RKPW101920 rack mount power strip is backed by a 2-year StarTech.com warranty with free technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **10 OUTLET RACK MOUNT POWER STRIP:** 10x 5-15/20R Outlets; 16 Amps; Max Input & Output: 125V; 8ft. NEMA 5-20P Power Cord; UL Listed PDU; For 19" Racks/Cabinets; Front-Facing Power Switch; Horizontal Mount
- **20 AMP CIRCUIT BREAKER:** This 10 outlet rackmount power strip features a built-in 20A circuit breaker, with included 8 ft long NEMA 5-20P to IEC 60320 C19 power cord
- **EASY INSTALLATION:** The rack-mount PDU with metal housing supports 19 inch rack 1U horizontal installation, and meets ANSI/EIA RS-310-D standards
- **BROAD COMPATIBILITY:** 1U horizontal rack-mounted power distribution unit fits many network / data 2-post and 4-post racks; Compatible with 19" server racks with minimum 4" (10.2cm) depth
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this rack mountable power bar is backed for 2-Years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	2 Years
U-Höhe	1U
Form Factor	Horizontal
Steckdosenkompatibilität	10
Einbaufähig	Ja

Leistung

Max. Eingangsstrom pro Phase	20A
Max. Gesamtstromaufnahme pro Phase	20A
Behördlich	16A

herabgesetzter Eingangsstrom (Nordamerika)	
Nominale Eingangsspannung	125V
Nominale Ausgangsspannung	125V
Max. Ausgangsspannung	125V
Belastbarkeit	2500VA

Steckverbinder

Eingangssteckverbinder	1 - IEC 60320 C20 Strom
Ausgangssteckverbinder	10 - NEMA 5-20R (North America)
	1 - IEC 60320 C19 Strom

Strom

Frequenz Eingangsspannung	50/60Hz
Eingangsspannung	125V (max.)
Eingangsstrom	16A (max.)
Ausgangsspannung	125V (max.)
Ausgangsstrom	16A (max.)
Steckertyp	NEMA 5-20P

Umgebungsbedingungen

Betriebstemperatur	0C to 40C
Lagertemperatur	-10C to 60C
Feuchtigkeit	5% (0C) to 95% (40C)

Physische Eigenschaften

Farbe	Schwarz
-------	---------

Gehäusotyp	Aluminium
Kabellänge	7.9 ft [2.4 m]
Produktlänge	5.1 in [13.0 cm]
Produktbreite	17.5 in [44.5 cm]
Produkthöhe	2.0 in [5.0 cm]
Produktgewicht	2.6 lb [1.2 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	6.5 in [16.5 cm]
Paketbreite	23.1 in [58.7 cm]
Pakethöhe	4.2 in [10.6 cm]
Versandgewicht (Verpackung)	3.4 lb [1.5 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Rackmount 10 Outlet Rackmountable Power Strip
	1 - 8 ft NEMA 5-20P to IEC 60320 C19 Power Cord
	1 - Kurzanleitung

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.