

## Rackmount PDU with 16 Outlets and Surge Protection - 1U

**Product ID:** RKPW161915



This 16-outlet (120V 15A)(12A UL) Rack PDU delivers a cost-effective power distribution solution for your server rack/cabinet. The 1U PDU can be mounted horizontally in any server rack 4in in depth or greater, to provide sixteen 120V 15A power ports/outlets, and features a rugged steel casing to ensure maximum durability.

The front of the PDU features two LEDs that indicate proper ground and surge detection, while enabling you to control the power state with an illuminated power/reset switch.

To prevent costly breakdowns of connected devices, the rackmount PDU features a built-in circuit breaker and reset switch, ensuring dependable performance of vital equipment.

### Certifications, Reports and Compatibility

### Applications

- 16 easily accessible power outlets in a compact 1U of rack space
- Localize the power control for all of your connected system

### Features

- Built in circuit breaker
- Illuminated reset and power switch
- Integrated 6ft power cord
- LED indicators for ground and surge detection

- Meets ANSI/EIA RS-310-D standards
- Solid Steel Chassis for durability

---

#### Hardware

Warranty	2 Years
Form Factor	Horizontal
Number of Power Outlets	16
Rack-Mountable	Yes

---

#### Performance

General Specifications	Surge Protection: 1800 Joules
Maximum Total Current	15A
Maximum Total Current Draw per Phase	15A
Regulatory Derated Input Current (North America)	12A
Nominal Input Voltage	120V
Nominal Output Voltage	120V
Maximum Output Voltage	125V
Load Capacity	1800VA

---

#### Connector(s)

Input Connector(s)	NEMA 5-15 Power (North America)
Output Connectors	NEMA 5-15 Power (North America)

---

#### Indicators

LED Indicators	Ground
	Surge

---

#### Power

Input Voltage	120 AC
---------------	--------

---

#### Environmental



Operating Temperature	-5C to 45C (23F to 113F)
Storage Temperature	-25C to 65C (-13F to 149F)
Humidity	0% RH

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	19.0 in [48.3 cm]
Product Width	3.8 in [95.5 mm]
Product Height	1.7 in [42.7 mm]
Weight of Product	4.4 lb [2.0 kg]

---

**Packaging Information**

Package Length	21.7 in [55.0 cm]
Package Width	8.0 in [20.4 cm]
Package Height	3.2 in [82.0 mm]
Shipping (Package) Weight	4.8 lb [2.2 kg]

---

**What's in the Box**

Included in Package	16 Port Power Distribution Unit
	Installation Manual

---

***\*Product appearance and specifications are subject to change without notice.***

