

## Declaration of Conformity

February 02, 2021

*To whom it may concern,*

I declare that this declaration is issued under the sole responsibility of StarTech.com and that the above product conforms to all the applicable requirements of Directives and Regulations as indicated in this document.

**Product Number:** RKPW161915

**Rackmount PDU with 16 Outlets and Surge Protection - 1U**



Nirav Gandhi  
*Vice President, Product Development*

**StarTech.com Ltd.**


**E** [prodcompliance@startech.com](mailto:prodcompliance@startech.com)

**T** (519) 455-9675

**T** (800) 265-1844

**F** (519) 455-9425



Regulations	Test Standards
<b>RoHS Directive</b> 2011/65/EU & 2015/863	This StarTech.com part number is in compliance with the European Directive 2011/65/EU on the Restriction of Hazardous Substances (RoHS) that include Pb, Hg, Cd, Cr6+, PBB, and PBDE.
<b>REACH Regulation</b> EC 1907/2006	The RoHS exemptions that apply to this product are: None  This product is also compliant with the REACH Regulation (EC) No. 1907/2006 of the European Parliament and of the Council of 18 December 2006, concerning the Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH). The product and its components do not contain any of the Candidate listed Substances of Very High Concern (SVHC) above the threshold of 0.1% by weight.
<b>Persistent Organic Pollutants (POPs)</b> EC No 850/2004	As per the EU Persistent Organic Pollutants Regulation (EC) No 850/2004 and Stockholm Convention, this StarTech.com product is free of the listed substance or falls under an exemption.
<b>WEEE Directive</b> EC No 850/2004	The European Directive 2012/19/EU on Waste Electrical and Electronic Equipment (WEEE)
<b>Packaging Directive</b> 94/62/EC	The European Packaging and Packaging Waste Directive 94/62/EC
<b>North American Safety</b>	
<b>UL Listing ID</b>	E234693
<b>UL Standard</b>	UL 60950-1, CAN/CSA C22.2 No. 60950-1
<b>Industry Canada (IC) Wireless ID</b>	UL 60950-1, CAN/CSA C22.2 No. 60950-1
<b>Australia Wireless ID</b>	UL 60950-1, CAN/CSA C22.2 No. 60950-1

