

3ft (1m) Power Extension Cord - 360° Rotating Flat Plug Extension Cord - NEMA 5-15P to NEMA 5-15R, 16 AWG, 125V/13A - Black Short 3-Prong Power Extender Cable

Produkt-ID: RTPAC1013



This 3 ft. Power Extension Cord features a rotating NEMA 5-15P to NEMA 5-15R connectors, maximizing the space available on your power strip, surge protector, or wall outlet.

Featuring a 360° rotating flat plug, this power cord extender enables you to easily connect your devices without damaging the cord. The flat plug design provides a convenient solution when connecting your devices in tight spaces.

The additional length provided by this three-foot cord allows for cleaner cable management when connecting powered devices.

Constructed with high-quality materials, the NEMA power cable is built with a 16 AWG wire suitable for high power connections.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

RTPAC1013 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend the connection distance between your PC, monitor, laser printer or scanner

Merkmale

- **360° ROTATING PLUG EXTENSION CABLE:** The 360 degree rotating flat plug extension cord can be positioned at any angle in tight areas; Ideal for use in a wall outlet or maximize space on power bars without blocking or interfering w/ other outlets
- **CONVENIENT FLAT PLUG:** Power extension cord w/ flat power plug design is ideal for wall sockets in space constrained areas such as behind desks or furniture close to the wall; Save more space in your home office setup by moving furniture closer to the wall
- **CERTIFIED POWER CORD:** This short 3ft extension cable with 16AWG wires is UL certified to ensure maximum safety for your devices and provide reliable power supply for all your electronics; 3-pronged plug with grounding wire provides additional protection
- Ausgelegt für 125 V bei 15 A
- **SPECS:** Length: 3 foot power extender cord | NEMA 5-15P (Plug) to (NEMA 5-15R (Socket) | 16AWG | 125V, 13A (Max) | Cable OD: 0.33" | Jacket: PVC | Color: Black | Lifetime Warranty

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Strom

Eingangsspannung	125 AC
Eingangsstrom	13 A

Umgebungsbeding

ungen

Betriebstemperatur	0°C to +40°C (32°F to 104°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0 % bis 90 % RH

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Gerade
Drahtstärke	16 AWG
Kabellänge	3.0 ft [0.9 m]
Produktlänge	3.4 ft [1.0 m]
Produktbreite	1.5 in [3.9 cm]
Produkthöhe	1.4 in [3.6 cm]
Produktgewicht	6.1 oz [172.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	11.3 in [28.7 cm]
Paketbreite	5.7 in [14.5 cm]
Pakethöhe	1.0 in [2.5 cm]
Versandgewicht (Verpackung)	6.3 oz [178.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - Netzkabel
--------------------	---------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.