

3ft (1m) Rugged Right Angle USB-C Cable, USB 3.2 Gen 2 (10 Gbps), Full-Featured USB C to C Data transfer Cable, 4K 60Hz DP Alt Mode, 100W Power Delivery - 90 Degree USB Type-C Cable

Product ID: RUSB31CC1MBR



Connect USB 10Gbps source and peripheral devices, using this 3.3ft (1m) Rugged Right Angle USB Type-C Cable. Position the right angle USB-C connection along the device to reduce cable clutter and avoid prolonged strain from bending.

It is ideal for 10Gbps data transfer to external USB-C-enabled external storage devices, or as a single-cable connection from a USB-C dock to a laptop.

The Rugged USB-C cable supports up to 4K 60Hz video over DisplayPort 1.2 Alt Mode, and is compatible with 1080p and lower resolutions.

Designed to withstand heavy use, the USB-C cable features an Aramid fiber core and durable TPE outer jacket. This heavy-duty construction protects against fraying or breakage and resists tangling.

This USB Type-C cable features Power Delivery (PD) 3.0 with up to 100W PD output. Power and charge a USB-C laptop, such as Apple MacBook, Lenovo ThinkPad, or Microsoft Surface with up to 100W output over USB Power Delivery 3.0. Connect the USB-C cable from a laptop to a USB-C wall charger or docking station.

Certifications, Reports and Compatibility



Applications

Features

- **RIGHT ANGLE USB CABLE:** Rugged USB Type-C Cable features a right angle USB-C connector; Ideal for connecting in tight spaces; 90 degree connector optimizes cable routing without placing unnecessary strain on the connector and device
- **DURABLE CONSTRUCTION:** The USB-C cable is reinforced with Aramid fiber to enhance flexibility and protection from frequent bending and wear; Robust strain reliefs with 8mm bend radius; Nickel-plated connectors rated beyond 10,000 insertion cycles
- **FULL-FEATURE USB-C:** Right angle USB-C cable supports up to 10 Gbps transfer rates, 4K 60Hz DP Alt Mode, and 100W Power Delivery; Universal compatibility between USB-C laptops, docking stations, UHD monitors, and external devices
- **THOUGHTFUL DESIGN:** Built-in E-Marker chip for consistent data, video, and Power Delivery output; Flexible TPE outer jacket is nontoxic, halogen-free, and RoHS compliant; Aluminum-mylar shield for enhanced EMI protection
- **PERFORMANCE:** USB 3.2 Gen 2 (10 Gbps); 4K 60Hz DP Alt Mode 1.2; 100W Power Delivery; 3.3ft (1m); Black; 4.8mm O.D.; Dock and charge a USB-C laptop over a single connection; Optimize cable routing to a USB-C device

Hardware

Warranty	2 Years
Active or Passive Adapter	Passive
Connector Plating	Gold and Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Video Revision	DisplayPort 1.2
Maximum Cable Length	3.3 ft [1 m]
Maximum Digital Resolutions	4K 60Hz
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s

Connector(s)

Connector A	1 - USB 3.2 Gen 2 USB Type-C (Power Delivery + Data, 24 Pin, 10 Gbps)
	1 - USB 3.2 Gen 2 USB Type-C (Power Delivery + Data, 24 Pin, 10 Gbps)

Special Notes /

Requirements

Note	USB 3.2 Gen 2 (10 Gbps) is also know as USB 3.1 Gen 2, USB 3.1, and SuperSpeed USB 10Gbps
------	---

Power

Power Delivery	100W
Output Current	5A

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0%~85% RH

Physical Characteristics

Color	Black
Connector Style	Right Angle to Straight
Cable Length	3.3 ft [1 m]
Cable OD	0.2 in [4.8 mm]
Product Length	3.3 ft [1.0 m]
Product Width	1.0 in [2.6 cm]
Product Height	0.2 in [6.3 mm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	5.0 in [12.8 cm]
Package Height	0.6 in [1.4 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

What's in the Box

Included in Package	1 - 1m Right Angled USB-C Cable
---------------------	---------------------------------

****Product appearance and specifications are subject to change without notice.***