

## 1m USB A to Lightning Cable - Durable Black USB Type A to Lightning Connector Charge and Sync Charger Cord - Rugged w/Aramid Fiber - Apple MFI Certified - iPad Air iPhone 11

Product ID: RUSBLTMM1MB



This USB to Lightning cable withstands the daily demands of charging and syncing your mobile devices. Tested to endure strenuous wear and tear and winter and summer in-car use, the rugged cable is a must-have for both business and consumer applications.

The durable Lightning cable has aramid fiber reinforcement that shelters it from the stress of frequent bends and twists. This also lets the cable flex without over-stretching, and strengthens the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil with braided shielding
- TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable and environmentally friendly

The cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle. Plus, the improved inner molding resists cracking and reduces cable damage.

- Lightning connector provides 12W for charging your iOS devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

RUSBLTMM1MB is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

*Note: DuPont and Kevlar are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.*

### Certifications, Reports and Compatibility



## Applications

- Charge and sync your Lightning mobile devices

## Features

- **DURABLE:** USB A to Lightning cable w/Kevlar aramid fiber for high tensile (pull) strength increasing reliability & life of cable. Tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions
- **FLEXIBLE CABLE:** TPE jacket absorbs stress of frequent bends without damaging the core of the cable. Durable wire & connector protects this charge & sync cable from wear & tear of frequent in-car use
- **APPLE MFI CERTIFIED:** Guaranteed fast & reliable charge from USB Type A charger/port for lightning devices incl iPhone 11 Pro, iPhone 11, iPhone XR, iPhone 8, iPad Air, iPad, iPad Mini
- **CHARGE LIGHTNING DEVICES:** Rugged charging cord is compatible with devices equipped with lightning port, incl AirPods, Magic Keyboard, Magic Trackpad, Magic Mouse and Siri Remote
- **CABLE SPECS:** Length: 1m (3ft) Color: Black Connectors: Lightning to USB A Performance: USB 2.0 480 Mbps Reinforcement: Aramid Fiber Jacket Type: TPE Shielding: EMI Protection Warranty: 2Yr

<b>Hardware</b>	Warranty	2 Years
	Connector Plating	Nickel
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	Apple Lightning Connector (8-pin)
<b>Physical Characteristics</b>	Color	Black
	Connector Style	Straight
	Wire Gauge	22/32 AWG
	Cable Length	39.4 in [10 cm]
	Product Length	39.4 in [10.0 cm]
	Product Width	0.5 in [13.000 mm]
	Product Height	0.2 in [6.000 mm]
	Weight of Product	0.5 oz [15.000 g]

---

<b>Packaging Information</b>	Package Length	4.9 in [1.2 cm]
	Package Width	3.0 in [75.000 mm]
	Package Height	0.6 in [15.000 mm]
	Shipping (Package) Weight	0.5 oz [15.000 g]

---

<b>What's in the Box</b>	Included in Package	USB to Lightning cable
--------------------------	---------------------	------------------------

---

*\*Product appearance and specifications are subject to change without notice.*

