

2m USB A to Lightning Cable - Durable 90 Degree Right Angled Black USB Type A to Lightning Connector Sync & Charger Cord w/Aramid Fiber Apple MFI Certified iPad iPhone 11

Product ID: RUSBLTMM2MBR



This angled Lightning to USB cable withstands the demands of charging and syncing your mobile devices. The angled Lightning connector gives you easy access to your mobile device, even while charging. And, the longer cable is ideal for overcoming distance restrictions.

With Kevlar aramid fiber reinforcement, the durable Lightning cable is sheltered from the stress of frequent bends and twists, which allows the cable to flex without over-stretching.

Aramid fiber adds strength and durability to the cable. Insulated conductors reduce friction, provide more flexibility. EMI (electromagnetic interference) protection with aluminum-mylar foil and braided shielding. TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable.

Constructed to prevent the connector from separating from the cable jacket, the extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle. Lightning connector provides 12W for charging your iOS devices. Metal shield protects circuit board from EMI and reinforces the connection point. Strain relief tested to tolerate over 10,000+ bend cycles at a 180-degree angle.

RUSBLTMM2MBR is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

Note: DuPont and Kevlar are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

Certifications, Reports and Compatibility



Applications

- Charge and sync your Lightning mobile devices
- Text, work, or game without the cable getting in the way
- Easy access in both portrait and landscape mode

Features

- **DURABLE:** USB A to lightning cable w/Kevlar aramid fiber for high tensile (pull) strength increasing reliability & cable life. Tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions
- **FLEXIBLE CABLE:** Built w/TPE jacket to absorb the stress of frequent bends while protecting the cable core. Durable wire & connector protects cable of wear & tear allowing for easy routing to tablet mount
- **RIGHT ANGLED CONNECTOR:** Eliminates tension & protects the lightning port of iPhone 11 Pro, iPhone 11, iPhone XR, iPad Air, iPad, iPad Mini. Ideal for car mounts, classroom desk mounts or mounted POS
- **APPLE MFI CERTIFIED:** Fast & reliable charge from USB-A charger/port to lightning devices, including AirPods, Magic Keyboard, Magic Trackpad, Magic Mouse. Supports USB 2.0 480 Mbps data transfers
- **CABLE SPECS:** Length: 2m (6ft) Color: Black Connectors: Angled Lightning to USB-A Performance: USB 2.0 Reinforcement: Aramid Fiber Jacket Type: TPE Shielding: EMI Protection Warranty: 2Yr

| | | |
|---------------------------------|-----------------------|-----------------------------------|
| Hardware | Warranty | 2 Years |
| | Connector Plating | Nickel |
| | Cable Jacket Material | TPE - Thermoplastic Elastomers |
| | Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Performance | Type and Rate | USB 2.0 - 480 Mbit/s |
| Connector(s) | Connector A | USB Type-A (4 pin) USB 2.0 |
| | Connector B | Apple Lightning Connector (8-pin) |
| Physical Characteristics | Color | Black |
| | Connector Style | Angled |
| | Wire Gauge | 22/32 AWG |
| | Cable Length | 6.6 ft [2 m] |
| | Product Length | 6.6 ft [2.0 m] |
| | Product Width | 1.0 in [26.100 mm] |
| | Product Height | 0.3 in [7.000 mm] |
| | Weight of Product | 1.6 oz [45.000 g] |
| Packaging Information | Package Length | 6.3 in [1.6 cm] |
| | Package Width | 3.0 in [75.000 mm] |
| | Package Height | 1.2 in [30.000 mm] |

| | |
|------------------------------|-------------------|
| Shipping (Package) Weight | 2.5 oz [71.000 g] |
|------------------------------|-------------------|

| | | |
|------------------------------|---------------------|---------------------|
| What's in the Box | Included in Package | 2 m Lightning Cable |
|------------------------------|---------------------|---------------------|

****Product appearance and specifications are subject to change without notice.***

