

## 2m USB A to Lightning Cable - Durable 90 Degree Right Angled White USB Type A to Lightning Connector Sync & Charger Cord w/Aramid Fiber Apple MFI Certified iPad iPhone 11

**Product ID:** RUSBLTMM2MWR

This angled Lightning to USB cable withstands the demands of charging and syncing your mobile devices. The angled Lightning connector gives you easy access to your mobile device, even while charging, and the longer cable is ideal for overcoming distance restrictions.

With Kevlar aramid fiber reinforcement, the durable Lightning cable is sheltered from the stress of frequent bends and twists, which allows the cable to flex without over-stretching.

Aramid fiber adds strength and durability to the cable. Insulated conductors reduce friction, provide more flexibility. EMI (electromagnetic interference) protection with aluminum-mylar foil and braided shielding. TPE (thermoplastic elastomer) cable jacket is softer and more flexible than a standard PVC cable.

Constructed to prevent the connector from separating from the cable jacket, the extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 degree angle.

Lightning connector provides 12W for charging your iOS devices. Metal shield protects circuit board from EMI and reinforces the connection point. Strain relief tested to tolerate over 10,000+ bend cycles at a 180-degree angle.

RUSBLTMM2MWR is an Apple MFi certified Lightning cable backed by a StarTech.com 2-year warranty.

Note: DuPont and Kevlar are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

## Certifications, Reports and Compatibility



## Applications

- Charge and sync your Lightning mobile devices
- Text, work, or game without the cable getting in the way
- Easy access in both portrait and landscape mode

## Features

- **DURABLE:** USB A to lightning cable w/Kevlar aramid fiber for high tensile (pull) strength increasing reliability & cable life. Tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions
- **FLEXIBLE CABLE:** Built w/TPE jacket to absorb the stress of frequent bends while protecting the cable core. Durable wire & connector protects cable of wear & tear allowing for easy routing to tablet mount
- **RIGHT ANGLED CONNECTOR:** Eliminates tension & protects the lightning port of iPhone 11 Pro, iPhone 11, iPhone XR, iPad Air, iPad, iPad Mini. Ideal for car mounts, classroom desk mounts or mounted POS
- **APPLE MFI CERTIFIED:** Fast & reliable charge from USB-A charger/port to lightning devices, including AirPods, Magic Keyboard, Magic Trackpad, Magic Mouse. Supports USB 2.0 480 Mbps data transfers
- **CABLE SPECS:** Length: 2m (6ft) Color: White Connectors: Angled Lightning to USB-A Performance: USB 2.0 Reinforcement: Aramid Fiber Jacket Type: TPE Shielding: EMI Protection Warranty: 2Yr

<b>Hardware</b>	Warranty	2 Years
	Connector Plating	Nickel
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	Apple Lightning Connector (8-pin)
<b>Physical Characteristics</b>	Color	White
	Connector Style	Angled
	Wire Gauge	22/32 AWG
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2.0 m]
	Product Width	5.3 in [1.4 cm]
	Product Height	2.0 in [50.000 mm]
	Weight of Product	1.6 oz [45.000 g]
<b>Packaging Information</b>	Package Length	7.2 in [1.8 cm]
	Package Width	3.0 in [75.000 mm]
	Package Height	1.2 in [30.000 mm]
	Shipping (Package) Weight	2.5 oz [72.000 g]
<b>What's in the Box</b>	Included in Package	2 m Lightning Cable

*\*Product appearance and specifications are subject to change without notice.*

