

10ft (3m) USB-C Charging Cable, Durable and Ultra-Flexible, 240W (5A) PD EPR, USB 2.0 Laptop Charger Cable, USB-IF Certified, Rugged USB-C Charging Cord

Produkt-ID: S2CEPR10F-USB-CABLE



Connect a charger or hub to a USB PD 3.1-enabled device with this USB-C cable, delivering up to 240W EPR Power Delivery and 5A output for fast charging. Clear connector markings ensure quick identification, eliminating guesswork and ensuring full 240W charging support. Always choose the correct Type-C cable for optimal performance and compatibility.

Rugged and Flexible

The USB-C EPR Charging Cable features a silicone inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 20,000 insertion cycles.

Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 10-foot (3-meter) USB Type-C cable is the ideal length for large desk and mobile workstations where extra reach is desired.

Power a Laptop

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **USB-C EPR CHARGING CABLE:** Rugged and flexible USB-C cable supports Power Delivery 3.1 EPR with up to 240W for high-performance laptops; Designed for reliable, high-power charging; Performance markings on connectors for easy identification
- **USB-IF CERTIFIED:** The USB C Cable with integrated E-marker chip is USB-IF certified, for safe and consistent Power Delivery output to USB-C hosts and peripherals; When using certified cables, reliable performance and compatibility is guaranteed
- **QUALITY CONSTRUCTION:** Dual-layer jacket features a silicone inner layer for optimal flexibility and a braided nylon exterior for rugged use; Designed to withstand frequent 90° bends; Nickel-plated connectors rated beyond 20,000 insertions
- **APPLICATIONS:** Compatible with USB-C Power Delivery-enabled devices; Suitable for charging mobile devices and high-performance laptops such as 16in MacBook Pro Max M-series; Supports USB 2.0 for general file transfer or sync
- **PERFORMANCE:** 240W (5A) PD 3.1 EPR, 48V; Compatible with 140W, 100W, 60W; USB 2.0 Type-C (480Mbps); 10-foot (3-meter) cable; Color: Black; O.D.: 0.18in (4.7mm); Dual-layer Silicone Jacket with Nylon Braid; NOTE: USB-C video (DP Alt Mode) not supported

Hardware

Garantiebestimmungen	Lifetime
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	Silicone with Braided Nylon

Leistung

MTBF	Für mehr als 10.000 Einfügungen ausgelegt
------	---

Steckverbinder

Steckverbinder A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Steckverbinder B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Strom

Power Delivery 240W

Umgebungsbedingungen

Betriebstemperatur 0°C - 50°C (32°F - 122°F)
Lagertemperatur -20°C - 70°C (-4°F - 158°F)
Feuchtigkeit 5% - 85%

Physische Eigenschaften

Farbe Schwarz
Steckverbinderart Gerade
Drahtstärke 30 AWG
Gehäusetyp ABS
Kabellänge 10.0 ft [3.0 m]
Außendurchmesser des Kabels 0.2 in [4.7 mm]
Produktlänge 120.6 in [3063.3 mm]
Produktbreite 0.5 in [12.3 mm]
Produkthöhe 0.3 in [6.8 mm]
Produktgewicht 5.4 oz [152.0 g]

Verpackungsinformationen

Paketlänge 5.0 in [12.8 cm]
Paketbreite 8.7 in [22.0 cm]
Pakethöhe 0.8 in [2.0 cm]
Versandgewicht (Verpackung) 5.6 oz [158.0 g]

Verpackungsinhalt

Im Paket enthalten 1 - 10ft Braided USB-C Charging Cable M/M

Garantieinformatio
nen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.