

6ft (1.8m) USB-C Charging Cable, Durable and Ultra-Flexible, 240W (5A) PD EPR, USB 2.0 Laptop Charger Cable, USB-IF Certified, Rugged USB-C Charging Cord

Product ID: S2CEPR6F-USB-CABLE



Connect a charger or hub to a USB PD 3.1-enabled device with this USB-C cable, delivering up to 240W EPR Power Delivery and 5A output for fast charging. Clear connector markings ensure quick identification, eliminating guesswork and ensuring full 240W charging support. Always choose the correct Type-C cable for optimal performance and compatibility.

Rugged and Flexible

The USB-C EPR Charging Cable features a silicone inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 20,000 insertion cycles.


Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 6-foot (1.8-meter) USB Type-C cable is the ideal length for desk and mobile workstations or when syncing with a USB-C laptop.

Power a Laptop

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Certifications, Reports and Compatibility



Applications

Features

- **Charge High-Draw USB-C Devices**: Charge high-performance laptops with up to 240W of Power Delivery Extended Power Range (EPR) using this rugged and flexible USB-C cable; Performance markings on connectors ensure quick identification and removes guesswork
- **Certified for Compatible and Safe Charging**: Trust this USB-IF Certified Cable with E-marker chip to ensure reliable power delivery in critical workflow; Certified cables guarantee safe, regulated charging across USB-C PD-enabled devices
- **Designed for Everyday Use**: Dual-layer jacket combines a silicone inner layer for flexibility with braided nylon exterior for enhanced durability; Designed to withstand frequent 90° bends, with nickel-plated connectors rated beyond 20,000 insertions
- **Connect to a High-Power Charging Hub**: Integrate high-wattage charging hubs into workstation setups with reliable support for mobile devices and high-performance laptops, including 16-in MacBook Pro Max M-series; Supports USB 2.0 for general file transfer or sync
- **The IT Pro's Choice**: Our USB-C cables are rigorously tested in our in-house Innovation Lab for reliable performance, durable construction, and broad compatibility with a variety of devices; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	Silicone with Braided Nylon

Performance

MTBF	Rated beyond 10,000 insertions
------	--------------------------------

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	240W
----------------	------

Environmental

Operating Temperature	0°degC - 50°degC (32°degF - 122°degF)
Storage Temperature	-20°degC - 70°degC (-4°degF - 158°degF)

Humidity	5% - 85%
----------	----------

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Material	Santoprene - Thermoplastic Rubber (TPE)
Cable Length	6.0 ft [1.8 m]
Cable OD	0.2 in [4.2 mm]
Product Length	72.6 in [1843.3 mm]
Product Width	0.5 in [12.3 mm]
Product Height	0.3 in [6.8 mm]
Weight of Product	2.6 oz [74 g]

Packaging Information

Package Length	5.0 in [12.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.7 in [1.8 cm]
Shipping (Package) Weight	3.0 oz [84.0 g]

What's in the Box

Included in Package	1 - 6ft Braided USB-C Charging Cable M/M
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*