

## 100 ft Cat5e Blue Snagless Shielded RJ45 F/UTP Cat 5e Patch Cable - 100ft Patch Cord

**Product ID:** S45PATCH100B



StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cables offer reliable Ethernet connections. This 100ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To reduce susceptibility to EMI/RFI and near end cross-talk, the patch cable is shielded throughout the length of the cable, as well as around the RJ45 connectors. Our Cat5e Shielded F/UTP Snagless Patch Cables also feature a snagless design that protects the RJ45 clip from snagging during installation, as well as PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage.

StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cable is constructed of top quality materials (100% copper conductors, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and performance, and backed by our Lifetime Warranty.

### **Certifications, Reports and Compatibility**

#### **Applications**

- Designed for Network Adapters, Hubs, Switches, Routers, DSL/Cable Modems and other applications requiring high-speed cables
- Works with 1000 BASE-T, 100 BASE-T, 10 BASE-T, Token Ring, ATM & ISDN networks
- Suited for all industrial applications

#### **Features**

- StarTech.com Category 5e shielded cables are manufactured to meet or exceed CAT5e specifications

- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification

---

**Hardware**

Warranty	Lifetime
Number of Conductors	4 pair F/UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Shielded Snag-less

---

**Performance**

Cable Rating	CAT5e - 350 MHz
--------------	-----------------

---

**Connector(s)**

Connector A	RJ-45
Connector B	RJ-45

---

**Physical Characteristics**

Color	Blue
Wire Gauge	24 AWG
Cable Length	100.0 ft [30.5 m]
Product Length	100.0 ft [30.5 m]
Weight of Product	2.4 lb [1.1 kg]

---

**Packaging Information**

Package Length	9.6 in [24.5 cm]
Package Width	2.8 in [70 mm]
Package Height	12.4 in [31.5 cm]
Shipping (Package) Weight	2.4 lb [1.1 kg]

---



***\*Product appearance and specifications are subject to change without notice.***

