

10 ft Cat5e Blue Snagless Shielded RJ45 STP Cat 5e Patch Cable - 10ft Patch Cord

Produkt-ID: S45PATCH10BL



StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cables offer reliable Ethernet connections. This 10ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To reduce susceptibility to EMI/RFI and near end cross-talk, the patch cable is shielded throughout the length of the cable, as well as around the RJ45 connectors. Our Cat5e Shielded F/UTP Snagless Patch Cables also feature a snagless design that protects the RJ45 clip from snagging during installation, as well as PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage.

StarTech.com's Cat5e Shielded F/UTP Snagless Patch Cable is constructed of top quality materials (100% copper conductors, 24 Gauge Wire, 50 micron Gold Connectors) to ensure optimum durability and performance, and backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Designed for Network Adapters, Hubs, Switches, Routers, DSL/Cable Modems and other applications requiring high-speed cables
- Works with 1000 BASE-T, 100 BASE-T, 10 BASE-T, Token Ring, ATM & ISDN networks

- Suited for all industrial applications

Merkmale

- StarTech.com Category 5e shielded cables are manufactured to meet or exceed CAT5e specifications
- Molded strain relief and stranded wires for added flexibility and durability
- Colored Hoods for departmental color coding and easy identification

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4-Pair STP
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck)e
Kabeltyp	Abgeschirmt, nahtlos geformt

Steckverbinder

Steckverbinder A	1 - RJ-45
Steckverbinder B	1 - RJ-45

Umgebungsbedingungen

Betriebstemperatur	0°C to 50°C (32°F to 122°F)
Lagertemperatur	-20°C to 70°C (-4°F to 158°F)
Feuchtigkeit	0-95% RH

Physische Eigenschaften

Farbe	Blau
Drahtstärke	24 AWG
Kabellänge	10.0 ft [3.0 m]

Produktlänge	10.0 ft [3.0 m]
Produktgewicht	4.3 oz [121 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	6.8 in [17.3 cm]
Paketbreite	7.8 in [19.8 cm]
Pakethöhe	1.1 in [2.9 cm]
Versandgewicht (Verpackung)	4.8 oz [136.0 g]

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.