

Extra 2.5in SATA Hard Drive Enclosure for SAT2510U2REM

Product ID: SAT2510U2S



This spare 2.5in removable SATA drive enclosure is designed for use with StarTech.com's 3.5in Bay Removable 2.5in SATA Drive Enclosure (SAT2510U2REM), providing additional external storage via USB 2.0, and in turn allowing multiple users to share and access files from a single desktop system.

The spare drive enclosure features a portable design that adds to the mobility of your data, making it convenient to access your files externally from a desktop or laptop computer, or to migrate data to similarly equipped desktops in another office, data center or home environment.

Certifications, Reports and Compatibility

Applications

- Use multiple hard drives with the same SAT2510U2REM installation for different scenarios/configurations or rotating backup disks
- Professionals working with large files who need to transport them between computers/locations
- Easily work on and store large presentations or demos from your desktop, then transport it to a clients location without having to transfer files between drives
- Business professionals who need first hand access to their office data while travelling
- Users who need both fast internal storage and portable external storage

Features

- Extra/replacement removable drive enclosure for SAT2510U2REM

- Unique enclosure design allows it to be used as an internal removable drive or as a regular external enclosure
- Powered directly from the USB port, when used externally
- Light-weight and durable aluminum construction for the drive enclosure
- High Speed USB 2.0 compliant host interface, with transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" form factor SATA hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible

Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 2.0
Number of Drives	1
Drive Size	2.5in
Compatible Drive Types	SATA
Drive Installation	Removable
Chipset ID	JMicron - JM20336

Performance

Type and Rate	USB 2.0 - 480 Mbit/s SATA II (3 Gbps)
Hardware Raid Supported	No
Max Drive Capacity	Tested up to 500 GB

Connector(s)

Connector Type(s)	SATA Power (15 pin) USB B (4 pin)
Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	SATA Data & Power Combo (7+15 pin)



USB Mini-B (5 pin)

Software

OS Compatibility	Windows 2000/ XP(32/64-bit)/ Vista(32/64-bit)/ 7(32/64-bit)/ 8 (32/64-bit), Mac OS X (tested up to 10.8) , Linux
------------------	--

Special Notes / Requirements

Note	This is an extra 2.5" hard drive enclosure for the SAT2510U2REM
------	---

Power

Power Source	Not Included (not required for standard applications)
Input Voltage	5 DC
Plug Type	F

Physical Characteristics

Color	Silver
Material	Aluminum and Plastic
Max Drive Height	0.4 in [9.5 mm]
Product Length	5.2 in [13.3 cm]
Product Width	3.1 in [79 mm]
Product Height	0.6 in [15 mm]
Weight of Product	3.5 oz [100 g]

Packaging Information

Package Length	7.3 in [18.5 cm]
Package Width	1.6 in [40 mm]
Package Height	6.0 in [15.2 cm]
Shipping (Package) Weight	9.9 oz [280 g]

What's in the Box

Included in Package	Hard Drive Enclosure
---------------------	----------------------

USB Cable

Screw Kit

****Product appearance and specifications are subject to change without notice.***

