

## 3.5in Black USB 2.0 to SATA External Hard Drive Enclosure

**Product ID:** SAT3510BU2V



This Black External Hard Drive Enclosure lets you install a 3.5in SATA hard drive for connection to a computer using USB 2.0 - a cost-effective storage solution for a wide variety of applications including file and application sharing between desktop and laptop computers, data archiving, or simply backing up existing hard drives to preserve data security. Large capacity drives (tested with up to 4TB) can be used to greatly enhance your computer's storage/backup capabilities.

Designed with modern computer systems in mind, the USB 2.0 SATA hard drive enclosure is compatible with the IT industry's newest 3.5in SATA (SATA, SATA II, SATA III) and features a sleek, sturdy aluminum casing that looks terrific next to any MAC or PC system.

The enclosure is compatible with a broad range of Windows operating systems, Mac OS 9.0 and up and Linux, as well as Apple's Mac OS X Leopard operating system - including its breakthrough automatic "Time Machine" backup feature.

## Certifications, Reports and Compatibility

### Applications

- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on extra storage to almost any USB enabled computer system
- Backup important data to an external storage device
- Share large files between computers quickly and securely without a network
- Retrieve data from old SATA drive, or turn the unused drive into additional external storage space

## Features

- High Speed USB 2.0 host interface, with supported transfer rates up to 480 Mbps
- Power/Activity LED indicator
- Light-weight and durable aluminum chassis
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) hard drives
- Supports 3.5" form factor SATA hard drives
- Plug-and-Play and Hot-Swap compatible

---

### Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 2.0
Number of Drives	1
Drive Size	3.5in
Compatible Drive Types	SATA
Drive Installation	Fixed
Chipset ID	SunplusIT - SPIF301

---

### Performance

Maximum Data Transfer Rate	480 Mbps
Type and Rate	USB 2.0 - 480 Mbit/s
UASP Support	No
Type and Rate	SATA II (3 Gbps)
Hardware Raid Supported	No
Max Drive Capacity	Currently tested with up to 4TB 5400 RPM hard drives

---

### Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
------------------	------------------------------------



Host Connectors	USB B (4 pin)
-----------------	---------------

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Indicators**

LED Indicators	Power/Activity (Green)
----------------	------------------------

---

**Power**

Power Source	AC Adapter Included
--------------	---------------------

Input Voltage	115V AC
---------------	---------

Output Voltage	12V DC
----------------	--------

Output Current	2A
----------------	----

Center Tip Polarity	Positive
---------------------	----------

Plug Type	M
-----------	---

---

**Environmental**

Operating Temperature	0C ~ 70C
-----------------------	----------

Storage Temperature	-20C ~ 70C
---------------------	------------

Humidity	5% ~ 95% RH
----------	-------------

---

**Physical Characteristics**

Color	Black
-------	-------

Material	Aluminum
----------	----------

Product Length	7.6 in [19.3 cm]
----------------	------------------

Product Width	1.2 in [31 mm]
---------------	----------------

Product Height	4.4 in [11.3 cm]
----------------	------------------

Weight of Product	11.5 oz [325 g]
-------------------	-----------------

---

**Packaging Information**

Package Length	10.3 in [26.2 cm]
----------------	-------------------

Package Width	3.7 in [95 mm]
---------------	----------------



Package Height	7.8 in [19.7 cm]
Shipping (Package) Weight	22.9 oz [650 g]

---

**What's in the Box**

Included in Package	3.5in SATA HDD Enclosure
	Plastic Stand
	USB 2.0 Cable
	Screw Kit
	Power Adapter
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

