

3.5in USB FireWire SATA External Hard Drive Enclosure

Product ID: SAT3510U2F



The SAT3510U2F External Hard Drive Enclosure supports both USB 2.0 and FireWire 400 (IEEE1394a) host connections, providing the compatibility needed to create a convenient and versatile external SATA storage solution for desktop computers as well as MacBooks and Windows based laptops. Large capacity drives (tested with up to 4TB) can be used to greatly enhance your computer's storage/backup capabilities.

The USB/FireWire enclosure features a slim, lightweight aluminum design and includes a 6-pin FireWire cable simplifying the option to connect through IEEE 1394a, as well as a USB cable for USB 2.0 connections to the host.

Certifications, Reports and Compatibility

Applications

- Create a fast, portable external storage solution for desktops, laptops or netbooks
- Add-on extra storage to almost any USB enabled computer system
- Backup important data to an external storage device
- Share large files between computers quickly and securely without a network
- Retrieve data from old SATA drive, or turn the unused drive into additional external storage space

Features

- IEEE 1394a compliant (FireWire 400) host interface, with supported transfer rates up to 400Mbps
- Dual 6-pin FireWire 400 ports for daisy-chaining support

- High Speed USB 2.0 host interface, with supported transfer rates up to 480 Mbps
- Light-weight and durable aluminum chassis
- Power/Activity LED indicator
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 3.5" form factor SATA hard drives (HDD)
- Plug-and-Play and Hot-Swap compatible

Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 2.0 & Firewire
Number of Drives	1
Drive Size	3.5in
Compatible Drive Types	SATA
Drive Installation	Fixed
Chipset ID	Initio - INIC-1615

Performance

Type and Rate	FireWire 400 IEEE-1394a - 400 Mbit/s USB 2.0 - 480 Mbit/s
UASP Support	No
Hardware Raid Supported	No
Max Drive Capacity	Currently tested with up to 4TB 5400 RPM hard drives

Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	FireWire 400 (6 pin, IEEE 1394a) USB B (4 pin)



Software

OS Compatibility OS independent; No software or drivers required

Indicators

LED Indicators Blue - Solid: Power, Blinking: Activity

Power

Power Source AC Adapter Included

Input Voltage 115V AC

Input Current 700mA

Output Voltage 12V DC

Output Current 2A

Center Tip Polarity Positive

Plug Type N

Environmental

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 60C (4F to 140F)

Humidity 0~90% RH

Physical Characteristics

Color Silver

Material Aluminum

Product Length 8.2 in [20.8 cm]

Product Width 4.6 in [11.8 cm]

Product Height 1.2 in [30 mm]

Weight of Product 14.1 oz [400 g]

Packaging Information

Package Length 11.8 in [29.9 cm]

Package Width 2.6 in [66 mm]



Package Height	7.1 in [18 cm]
Shipping (Package) Weight	31.1 oz [880 g]

What's in the Box

Included in Package	3.5" SATA Hard Drive Enclosure
	Plastic Stand
	6pin FireWire Cable
	USB A to B Cable
	Power Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

