

## Dual 3.5in USB 3.0 Hot Swap Trayless SATA Hard Drive Enclosure w/ Fan

Produkt ID: SAT3520U3R



The SAT3520U3R USB 3.0 to Dual 3.5-inch SATA Trayless Hard Drive Enclosure makes adding fast external storage easy, by turning any two 3.5-inch internal SATA hard drives into an external hard drive. Large capacity drives (tested with up to 4TB per bay) can be used to greatly enhance your computer's storage/backup capabilities.

The hard drive enclosure features a trayless system that eliminates having to mount and fasten the hard drive into the enclosure or tray, for quick and easy installation or removal.

Using the SuperSpeed USB 3.0 interface, which is up to 10 times faster than the previous USB 2.0, makes backing up and transferring large files faster than ever, while still being usable on older USB 2.0 systems. With built-in RAID capabilities (0, 1, BIG, JBOD), the two drives can be combined for speed, redundancy, capacity, or even left as separate drives, based on situation needs.

### Certifikat, rapporter och kompatibilitet

#### Användning

- Adding external storage that is easily transferable between different computer systems
- Expand the storage capabilities of a small form factor/embedded system or laptop, with an external hard drive
- Adding external storage capacity for video editing or photo editing stations, making it easier to work with very large file sizes
- Creating additional backup/archive storage for IT professionals

- Turning unused SATA hard drives into additional external data storage

## Funktioner

- Trayless design: 3.5in drives are not mounted to a tray or the enclosure chassis/frame
- SuperSpeed USB 3.0 compliant host interface, which supports transfer rates up to 5 Gbps
- RAID support: 0, 1, BIG (Concatenation), JBOD
- Backward compatible with USB 2.0 systems, out of the box
- 55mm cooling fan
- Lockable drive doors
- Power and Activity LED indicators
- Plug-and-Play and Hot-Swap compatible

---

### Hårdvara

Garantipolicy	2 Years
Fläkt(ar)	Ja
Flaktar	55 mm
Gränssnitt	USB 3.0
Antal enheter	2
Enhetsstorlek	3.5in
Enhetstyp	SATA
Enhetsinstallation	Löstagbar
Chipset-ID	JMicron - JMS551

---

### Prestanda

Typ och hastighet	USB 3.0 - 5 Gbit/s
UASP-stöd	Nej
Typ och hastighet	SATA II (3 Gbps)



RAID	Ja
RAID-lägen som stöds	BIG (Omfång eller sammanfogning) JBOD - (Just a Bunch of Disks) RAID 0 (stripade enheter) RAID 1 (speglade enheter)
Maximal enhetskapacitet	Currently tested with up to 4TB 5400 RPM hard drives per bay (8TB total)
Inläkningshastighet	15, 000 cycles
Temperaturlarm	Nej

---

#### Kontakt(er)

Enhetskontakter	SATA data- & ström-kombo (7+15-stifts)
Värdkontakter	USB Type-B (9-stifts) USB 3.0

---

#### Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

---

#### Särskilda anmärkningar/krav

System- och kabelkrav	Available USB port
-----------------------	--------------------

---

#### Indikatorer

LED-indikatorer	Power (blue) Activity (blue)
-----------------	---------------------------------

---

#### Ström

Power Source	AC-adapter medföljer
Inspänning	110V-240V AC
Utspänning	12V DC
Utström	3A

---

#### Miljö



Drifttemperatur	5°C to 80°C (41°F to 176°F)
Förvaringstemperatur	-40°C to 70°C (-40°F to 158°F)
Luftfuktighet	8% ~ 90% RH

---

Utseende

Färg	Svart
Kabinettyp	Aluminium och plast
Produktlängd	8.3 in [21 cm]
Produktbredd	3.0 in [76 mm]
Produkt höjd	5.3 in [13.5 cm]
Produktvikt	30.3 oz [858 g]

---

Förpackning

Förpackningsantal	1
Package Length	10.0 in [25.5 cm]
Package Width	5.5 in [13.9 cm]
Package Height	7.1 in [18 cm]
Fraktvikt (förpackning)	3.4 lb [1.5 kg]

---

Vad det är i lådan

Ingår i paketet	Hard Drive Enclosure
	USB 3.0 Cable
	Power Cord (NA/UK/EU)
	Universal Power Adapter
	Instruction Manual

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

