

12in Right Angle SATA Cable - Serial ATA F/F

Product ID: SATARA12



The SATARA12 Right Angle (90-degree) SATA cable (12in) enables you to plug in your SATA hard drive in hard to reach areas or tight spaces, using right-angled SATA connectors to reduce the amount of space required at the connection point and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance, and reliability this right angle SATA cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

Features

- 2x Right-Angled/90-degree SATA connectors
- Supports full SATA 3.0 6Gbps bandwidth

- Provides 12" in cable length

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Type and Rate	SATA III (6 Gbps)
---------------	-------------------

Connector(s)

Connector A	SATA (7 pin, Data)
Connector B	SATA (7 pin, Data)

Physical Characteristics

Color	Red
Connector Style	Right Angled
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]
Weight of Product	0.5 oz [14.5 g]

Packaging Information

Package Quantity	1
Package Length	9.1 in [23.2 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [10 mm]
Shipping (Package) Weight	0.5 oz [15.5 g]

What's in the Box

Included in Package	12in Right Angle SATA Cable - F/F
---------------------	-----------------------------------

**Product appearance and specifications are subject to change without notice.*