

18in Right Angle SATA Cable - F/F

Produkt ID: SATARA18



The SATARA18 Right Angle (90-degree) SATA cable (18in) enables you to plug in your SATA hard drive in hard to reach areas or tight spaces, using right-angled SATA connectors to reduce the amount of space required at the connection point and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance, and reliability this right angle SATA cable is backed by our lifetime warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

Funktioner



- 2x Right-Angled/90-degree SATA connectors
- Supports full SATA 3.0 6Gbps bandwidth
- Provides 18" in cable length

Hårdvara

Garantipolicy	Lifetime
Kabelmanteltyp	PVC - Polyvinyl Chloride

Prestanda

Typ och hastighet	SATA III (6 Gbps)
-------------------	-------------------

Kontakt(er)

Connector A	SATA (7-stifts, data)
Connector B	SATA (7-stifts, data)

Utseende

Färg	Röd
Kontakttyp	Högervinklad
Kabellängd	18.0 in [45.7 cm]
Produktvikt	0.3 oz [8 g]

Förpackning

Package Length	5.1 in [13 cm]
Package Width	0.6 in [14 mm]
Package Height	8.7 in [22.2 cm]
Fraktvikt (förpackning)	0.7 oz [20 g]

Vad det är i lådan

Ingår i paketet	18in Right Angle SATA Cable
-----------------	-----------------------------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.