

24in Right Angle SATA Cable

ID del Producto: SATARA24



The SATARA24 Right Angle (90-degree) SATA cable (24in) enables you to plug in your SATA hard drive in hard to reach areas or tight spaces, using right-angled SATA connectors to reduce the amount of space required at the connection point and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance, and reliability this right angle SATA cable is backed by our lifetime warranty.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

Características

- 2x Right-Angled/90-degree SATA connectors
- Supports full SATA 3.0 6Gbps bandwidth
- Provides 24" in cable length

Hardware

Política de Garantía	Lifetime
Cable Tipo Jacket	PVC - Polyvinyl Chloride

Rendimiento

Tipo y Velocidad	SATA III (6 Gbps)
------------------	-------------------

Conector(es)

Conector A	1 - SATA (7 pines, datos)
Conector B	1 - SATA (7 pines, datos)

Características Físicas

Color	Rojo
Estilo de Conector	Acodado a la Derecha
Longitud del Cable	24.0 in [609.6 mm]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	4.8 in [12.3 cm]
Ancho de la Caja	0.6 in [14 mm]
Altura de la Caja	8.6 in [21.8 cm]
Peso (de la Caja) del Envío	0.1 lb [0.0 kg]

Contenido de la

Caja

Incluido en la Caja

1 - 24in Right Angle SATA Cable

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.