

24in Right Angle SATA Cable

Productcode: SATARA24



The SATARA24 Right Angle (90-degree) SATA cable (24in) enables you to plug in your SATA hard drive in hard to reach areas or tight spaces, using right-angled SATA connectors to reduce the amount of space required at the connection point and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance, and reliability this right angle SATA cable is backed by our lifetime warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

Eigenschappen



- 2x Right-Angled/90-degree SATA connectors
- Supports full SATA 3.0 6Gbps bandwidth
- Provides 24" in cable length

Hardware

Garantiebeleid	Lifetime
Type kabelmantel	PVC - Polyvinyl Chloride

Prestaties

Type en snelheid	SATA III (6 Gbps)
------------------	-------------------

Connector(en)

Connector A	SATA (7-polig, data)
Connector B	SATA (7-polig, data)

Fysieke eigenschappen

Kleur	Rood
Stijl connector	Haaks met hoek naar rechts
Kabellengte	24.0 in [61.0 cm]

Verpakkingsinformatie

Package Length	4.8 in [12.3 cm]
Package Width	0.6 in [14 mm]
Package Height	8.6 in [21.8 cm]
Verzendgewicht (verpakt)	1.1 oz [30 g]

Wat wordt er meegeleverd

Meegeleverd	24in Right Angle SATA Cable
-------------	-----------------------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.