

36in Right Angle SATA Cable

ID del Producto: SATARA36



The SATARA36 Right Angle (90-degree) SATA cable (36in) enables you to plug in your SATA hard drive in hard to reach areas or tight spaces, using right-angled SATA connectors to reduce the amount of space required at the connection point and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance, and reliability this right angle SATA cable is backed by our lifetime warranty.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases
- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays

Características

- 2x Right-Angled/90-degree SATA connectors
- Supports full SATA 3.0 6Gbps bandwidth
- Provides 36" in cable length

Hardware

Política de Garantía	Lifetime
Cable Tipo Jacket	PVC - Polyvinyl Chloride

Rendimiento

Tipo y Velocidad	SATA III (6 Gbps)
------------------	-------------------

Conector(es)

Conector A	1 - SATA (7 pines, datos)
Conector B	1 - SATA (7 pines, datos)

Características Físicas

Color	Rojo
Longitud del Cable	36.0 in [914.4 mm]
Longitud del Producto	36.0 in [914.4 mm]

Información de la Caja

Longitud de la Caja	4.7 in [12 cm]
Ancho de la Caja	0.6 in [14 mm]
Altura de la Caja	8.5 in [21.7 cm]
Peso (de la Caja) del Envío	0.1 lb [0.0 kg]

Contenido de la Caja

Incluido en la Caja	1 - 36in Right Angle SATA Cable
---------------------	---------------------------------

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.