

36in Right Angle SATA Cable

Product ID: SATARA36



The SATARA36 Right Angle (90-degree) SATA cable (36in) enables you to plug in your SATA hard drive in hard to reach areas or tight spaces, using right-angled SATA connectors to reduce the amount of space required at the connection point and supports full SATA 3.0 bandwidth of up to 6Gbps when used with SATA 3.0 compliant drives.

Featuring a low profile, yet durable construction, the flexible design improves airflow and reduces clutter in your computer case, helping to keep the case clean and cool.

Constructed of only top quality materials and designed for optimum performance, and reliability this right angle SATA cable is backed by our lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Server and storage subsystem applications
- High-end workstation drive installations
- Connections to SATA Drive Arrays
- Installing Serial ATA hard drives, and DVD drives in Small Form Factor computer cases

Features

- Provides 36" in cable length
 - Supports full SATA 3.0 6Gbps bandwidth
 - 2x Right-Angled/90-degree SATA connectors
-

Hardware	Warranty	Lifetime
	Type kabelmantel	PVC - Polyvinyl Chloride
Prestaties	Type en snelheid	SATA III (6 Gbps)
Connector(en)	Connector A	SATA (7 pin, Data)
	Connector B	SATA (7 pin, Data)
Fysieke eigenschappen	Kleur	Red
	Kabellengte	36.0 in [9.1 cm]
	Lengte product	36.0 in [9.1 cm]
Verpakkingsinformatie	Package Length	4.7 in [1.2 cm]
	Package Width	0.6 in [14 mm]
	Package Height	8.5 in [2.2 cm]
	Verzendgewicht (verpakt)	1.1 oz [30 g]
Wat wordt er meegeleverd	Meegeleverd	36in Right Angle SATA Cable

**Product appearance and specifications are subject to change without notice.*

