

## eSATA USB to SATA External HDD Dock for Dual 2.5 or 3.5in Hard Drive

**Product ID:** SATDOCK2UEEU



This dual drive SATA HDD Dock provides fast, convenient access to 2.5" or 3.5" SATA (SATA , SATA II, SATA III) hard drive (HDD) or solid state drives (SSD) contents through either USB or eSATA, without ever having to open a computer case or mount hard drives in an enclosure.

Supporting one or two drives (tested with up to 4TB 3.5" and 1TB 2.5" drives per bay), SATDOCK2UEEU can be connected to the host computer through either USB 2.0 or eSATA - then, it's just a matter of inserting the desired 2.5" or 3.5" SATA drives (or combination of both) into one of the two (or both) docking station slots for instant access.

The docking station supports plug and play installation on most operating systems, making it a perfect solution for data recovery, drive imaging, software testing, or any environment that requires fast access to massive amounts of data (uninstalled or archived hard drives etc.). Plus, SATDOCK2UEEU features a small form factor design that requires minimal desk space for permanent connection to the host computer and provides enough hard drive surface exposure to optimize dissipation of operating heat.

SATDOCK2UEEU supports any 2.5" or 3.5" SATA drives and data transfer speeds of up to 1.5 Gbps (using eSATA) and 480Mbps (using USB 2.0) between host and dock - ensuring effortless data dumps or backups and hassle-free file transfers.

## Certifications, Reports and Compatibility

### Applications

- Access spare or removed 2.5/3.5" drives quickly to retrieve data from
- Data recovery specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving

- Technicians who regularly test or benchmark different hard drives and need to swap between them
- Transfer data from one hard drive to another from the same dock

## Features

- Dual top slot loading design with drive doors
- Patented drive ejection mechanism for each drive
- Power button with integrated Power/Activity LED indicator for each drive
- Dual SATA revision 1 compliant eSATA host interfaces, with support for transfer rates up to 1.5 Gbps for each drive
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" or 3.5" form factor hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- Compact desktop style form factor

---

### Hardware

Warranty	2 Years
Fan(s)	No
Interface	USB 2.0 & eSATA
Number of Drives	2
Drive Size	2.5in & 3.5in
Compatible Drive Types	SATA

---

### Performance

Type and Rate	USB 2.0 - 480 Mbit/s
UASP Support	No
Type and Rate	SATA II (3 Gbps)
Max Drive Capacity	Currently tested with up to 4TB 5400 RPM 3.5" hard drives per bay (8TB total) and 1TB 5400 RPM 2.5" hard drives (2TB total)

---

### Connector(s)



Drive Connectors	SATA Data & Power Combo (7+15 pin)
Host Connectors	eSATA (7 pin, Data) USB B (4 pin)

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Indicators**

LED Indicators	Power/Activity
----------------	----------------

---

**Power**

Power Source	AC Adapter Included
Input Voltage	115V-230V AC
Output Voltage	12/5V DC
Output Current	3A

---

**Physical Characteristics**

Color	Black
Material	Plastic
Product Length	5.8 in [14.7 cm]
Product Width	5.2 in [13.2 cm]
Product Height	2.8 in [70 mm]
Weight of Product	19.3 oz [547 g]

---

**Packaging Information**

Package Length	7.3 in [18.5 cm]
Package Width	4.7 in [12 cm]
Package Height	8.3 in [21 cm]
Shipping (Package) Weight	28.9 oz [820 g]

---

**What's in the Box**

Included in Package	SATA hard drive docking station
---------------------	---------------------------------

eSATA Cable

USB Cable

Power Adapter

Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

