

eSATA USB to SATA External HDD Docking Station for 2.5 or 3.5in

Produkt ID: SATDOCKU2EEU



This eSATA/USB to SATA External HDD Docking Station provides immediate, swappable access to any 2.5in or 3.5in SATA (SATA, SATA II, SATA III) hard drive or solid state drive - without having to mount the hard drive, or install it in an enclosure! Large capacity drives (tested with up to 4TB 3.5" and 1TB 2.5" drives) can be used to greatly enhance your computer's storage/backup capabilities.

Simply connect this docking station to a computer using either eSATA or USB 2.0, and it's as simple as inserting your 2.5in or 3.5in SATA hard drive into the dock whenever needed.

A perfect solution for data recovery, drive imaging, and testing centers, or any environment that requires fast access to uninstalled/archived drives, the SATA HDD Dock supports plug and play installation on most operating systems. Plus, the HDD docking station supports data transfer speeds of up to 3 Gbps (using eSATA) and 480Mbps (using USB 2.0) between host and dock - ensuring effortless data dumps, backups and hassle-free file transfers. Double the value of this hard drive docking station, using a SATA to IDE hard drive adapter (SAT2IDEADP), which enables you to use any 2.5 or 3.5in IDE hard drive in a SATA hard drive dock slot.

Certifikat, rapporter och kompatibilitet

Användning

- Access spare or removed 2.5/3.5" drives quickly to retrieve data from
- Data recovery specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving

- Technicians who regularly test or benchmark different hard drives and need to swap between them
- Take advantage of new laptops and desktops with USB 3.0 connectivity

Funktioner

- Top slot loading design with drive door
- Power/Activity LED indicator
- SATA revision 2 compliant eSATA host interface, with support for transfer rates up to 3 Gbps
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" or 3.5" form factor hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- Compact desktop style form factor

Hårdvara

Garantipolicy	2 Years
Fläkt(ar)	Nej
Gränssnitt	USB 2.0 & eSATA
Antal enheter	1
Enhetsstorlek	2.5in & 3.5in
Enhetsstyp	SATA
Chipset-ID	JMicron - JM20336

Prestanda

Typ och hastighet	USB 2.0 - 480 Mbit/s
UASP-stöd	Nej
Typ och hastighet	SATA II (3 Gbps)
Maximal enhetskapacitet	Currently tested with up to 4TB 5400 RPM 3.5" hard drives and 1TB 5400 RPM 2.5" hard drive



Inlänkingshastighet 15, 000 cycles

Kontakt(er)

Enhetskontakter	SATA data- & ström-kombo (7+15-stifts)
Värdkontakter	eSATA (7-stifts, data)
	USB B (4-stifts)

Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

Indikatorer

LED-indikatorer	Power/Activity
-----------------	----------------

Ström

Power Source	AC-adapter medföljer
Inspänning	230 AC
Utspänning	12V DC
Utström	2A
Polaritet på mittpol	Positiv
Kontakttyp	M

Utseende

Färg	Svart
Kabinettyp	Av plast
Produktlängd	5.5 in [14 cm]
Produktbredd	3.6 in [91 mm]
Produkt höjd	2.2 in [55 mm]
Produktvikt	7.8 oz [221 g]

Förpackning

Package Length	6.5 in [16.4 cm]
----------------	------------------



Package Width	3.6 in [92 mm]
Package Height	6.8 in [17.2 cm]
Fraktvikt (förpackning)	29.7 oz [840 g]

Vad det är i lådan

Ingår i paketet	SATA hard drive docking station
	eSATA Cable
	USB Cable
	Power Adapter
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

