

USB to SATA External HDD Dock for 2.5 or 3.5in Hard Drive

Product ID: SATDOCKU2GB



This external hard drive dock adapter functions as a SATA HDD docking station - providing full, instant access to any 2.5in or 3.5in SATA (SATA, SATA II, SATA III) hard drive or solid state drive - without having to mount the hard drive in a computer or install it in an enclosure! Large capacity drives (tested with up to 4TB 3.5" and 1TB 2.5" drives) can be used to greatly enhance your computer's storage/backup capabilities.

Simply connect the hard drive dock to a host computer through USB 2.0, then insert a SATA hard drive into the dock whenever needed. To uninstall or swap the hard drive, just remove it from the dock!

The USB to SATA External HDD Dock Adapter supports plug and play hard drive installation on most operating systems, and offers data transfer speeds of up to 480Mbps - providing a convenient alternative to external hard drive enclosures and saving the time needed to prepare the drive for conventional installation. Double the value of this hard drive docking station, using a SATA to IDE hard drive adapter (SAT2IDEADP), which enables you to use any 2.5 or 3.5in IDE hard drive in a SATA hard drive dock slot.

Certifications, Reports and Compatibility



Applications

- Access spare or removed 2.5/3.5" drives quickly to retrieve data from

- Data recovery specialists who need quick access to drives for imaging
- Backup data quickly to an external drive for archiving
- Technicians who regularly test or benchmark different hard drives and need to swap between them
- Take advantage of new laptops and desktops with USB 3.0 connectivity

Features

- Top slot loading design with drive door
- Power/Activity LED indicator
- High Speed USB 2.0 compliant host interface, with support for transfer rates up to 480 Mbps
- Compatible with SATA revision 1/2/3 (1.5/3.0/6.0 Gbps) drives
- Supports 2.5" or 3.5" form factor hard drives (HDD) and solid state drives (SSD)
- Plug-and-Play and Hot-Swap compatible
- Compact desktop style form factor

Hardware

| | |
|------------------------|---------------|
| Warranty | 2 Years |
| Fan(s) | No |
| Interface | USB 2.0 |
| Number of Drives | 1 |
| Drive Size | 2.5in & 3.5in |
| Compatible Drive Types | SATA |

Performance

| | |
|----------------------------|--|
| Maximum Data Transfer Rate | 480 Mbps |
| Type and Rate | USB 2.0 - 480 Mbit/s |
| UASP Support | No |
| Max Drive Capacity | Currently tested with up to 4TB 5400 RPM 3.5" hard drives and 1TB 5400 RPM 2.5" hard drive |

Connector(s)

| | |
|------------------|--|
| Drive Connectors | 1 - SATA Data & Power Combo (7+15 pin) |
| Host Connectors | 1 - USB B (4 pin) |

Software

| | |
|------------------|---|
| OS Compatibility | Windows 2000/ XP(32/64bit)/ Server 2003(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)/ Server 2008 R2, Linux, and MAC OS X and up |
|------------------|---|

Indicators

| | |
|----------------|--------------------|
| LED Indicators | 1 - Power/Activity |
|----------------|--------------------|

Power

| | |
|---------------------|---------------------|
| Power Source | AC Adapter Included |
| Input Voltage | 230 AC |
| Output Voltage | 12V DC |
| Output Current | 2A |
| Center Tip Polarity | Positive |
| Plug Type | M |

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Material | Plastic |
| Product Length | 5.5 in [14 cm] |
| Product Width | 3.6 in [9.1 cm] |
| Product Height | 2.2 in [5.5 cm] |
| Weight of Product | 7.8 oz [220 g] |

Packaging Information

| | |
|----------------|------------------|
| Package Length | 6.7 in [17 cm] |
| Package Width | 3.6 in [92 mm] |
| Package Height | 6.8 in [17.3 cm] |

| | |
|------------------------------|-----------------|
| Shipping (Package) Weight | 1.1 lb [0.5 kg] |
|------------------------------|-----------------|

What's in the Box

| | |
|---------------------|-------------------------------------|
| Included in Package | 1 - SATA hard drive docking station |
| | 1 - USB Cable |
| | 1 - Power Adapter |
| | 1 - Instruction Manual |

Warranty Information

| | |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

****Product appearance and specifications are subject to change without notice.***