

Standalone 2.5 / 3.5" SATA Hard Drive Duplicator w/ Multi HDD / SSD Image Backup Library

Product ID: SATDUP11IMG



The SATDUP11IMG standalone SATA hard drive duplicator, lets you create an exact duplicate of a SATA hard drive (HDD) / solid state drive (SSD), or create a single backup library drive containing multiple images you can copy to additional drives at any time.

Reduce clutter with the SATDUP11IMG eliminating the number of drives required when creating backups of multiple unique drive images. Using a single backup library drive, you can store several unique drive images on a single SSD / HDD, ensuring fast duplication at 6 GBpm and minimal clutter. This is an ideal solution if you frequently re-image different computer systems, because it means you'll only have to carry a single backup library drive to restore multiple drive images onto different systems.

The versatile duplicator also offers standard one-to-one drive duplication in three different modes: file & system copy, all partitions copy and whole copy. This is ideal for one-time drive duplication, eliminating the hassle of creating a drive image for a one-time project.

With an easy-to-read LCD display and intuitive four-button menu operation, the SATDUP11IMG ensures hassle-free setup and control. The menu gives you push-button access to many value-added features that ensure simple task management such as: drive to drive duplication, drive to Image library backup and restore, and many more. It also provides numerous advanced setup options for experienced users.

For added compatibility with different drive types in duplication, the SATDUP11IMG supports the use of various drive adapters. The below list of StarTech.com adapters have been specifically tested, to ensure compatibility with this drive duplicator:

2.5/3.5in IDE drives - SAT2IDEADP
mSATA drives - SAT2MSAT25
M.2 (NGFF) drives - SAT32M225

The SATDUP11IMG is TAA compliant and backed by a 2-year StarTech.com warranty and lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Forensic investigators who require disk sector imaging/cloning to create an exact replica of a source drive onto a different drive
- Professionals who require identical backups for when data integrity is crucial, such as data recovery
- Clone hard drives that contain hidden partitions, that some software disk cloning programs may skip
- System builders / IT specialists who require multiple unique drive images for different types of system builds

Features

- Supports 2.5in or 3.5in form factor hard drives (HDD) or solid state drives (SSD)
- Digital LCD Display for operation and task progress
- Supports SATA revision I/II/III (1.5/3.0/6.0 Gbps) drives
- Universal Power Adapter (NA/UK/EU)
- TAA Compliance (Trade Agreement Act)
- Three modes of hard drive duplication including Sector-by-Sector at 6 GBpm
- Multi-image library drive for hassle-free duplication

Hardware

Warranty	2 Years
Interface	SATA
Number of Drives	2
Drive Size	2.5in & 3.5in
Compatible Drive Types	SATA

Performance

Type and Rate	SATA III (6 Gbps)
Duplication Modes	System and File
	All Partitions
	Sector by Sector (Whole Drive)
	Percentage Copy



Duplication Speed	6GBpm
Max Drive Capacity	Currently tested with up to 6TB 7200 RPM 3.5" hard drives per bay and 1TB 7200 RPM 2.5" hard drives per bay

Connector(s)

Drive Connectors	SATA Data & Power Combo (7+15 pin)
------------------	------------------------------------

Software

OS Compatibility	OS independent; No software or drivers required
------------------	-------------------------------------------------

Special Notes / Requirements

Note	For duplication, the destination drive must be of equal or greater size than the source drive.
------	------------------------------------------------------------------------------------------------

Indicators

LED Indicators	Source Drive Power Indicator
	Source Drive Activity Indicator
	Source Drive Error Indicator
	Destination Drive Power Indicator
	Destination Drive Activity Indicator
	Destination Drive Error Indicator
	LCD Display

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1.4A
Output Voltage	12V DC
Output Current	5A
Center Tip Polarity	Positive
Power Consumption (In Watts)	60

Environmental



Operating Temperature	5C to 45C (41F to 113F)
Storage Temperature	-20C to -85C (-4F to 185F)
Humidity	20% ~ 80%

Physical Characteristics

Material	Steel
Product Length	5.1 in [12.9 cm]
Product Width	3.0 in [77 mm]
Product Height	1.1 in [28 mm]
Weight of Product	12.4 oz [350 g]

Packaging Information

Package Length	10.5 in [26.7 cm]
Package Width	7.3 in [18.5 cm]
Package Height	4.7 in [11.9 cm]
Shipping (Package) Weight	3.8 lb [1.7 kg]

What's in the Box

Included in Package	1:1 HDD/SSD Duplicator
	Universal power adapter (UK/NA/EU)
	Short SATA cable
	Long SATA cable
	eSATA + 12V power cable (Type M power connector)
	eSATA + 5V power cable (Type F power connector)
	HDD/SSD pads
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***