

## MSA Compliant SFP+ Transceiver Module - 10GBase-BX (Downstream)

**Product ID:** SFP-10GB-BX-D-STA-ST



The SFP-10GB-BX-D-STA-ST is a MSA compliant downstream fiber SFP+ transceiver which pairs with StarTech.com's SFP-10GB-BX-U-STA-ST. They are designed, programmed and tested to work with 10GBase-BX compatible MSA switches and routers. The SFP+ transceiver module supports a maximum distance of up to 10 km (6.2 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

### Technical Specifications:

- Wavelength: 1330nmTx/1270nmRx
- Maximum Data Transfer Rate: 10Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- Power Consumption: < 1.3W
- DDM: Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

## Applications

## Features

- **MSA UNCODED SFP+ TRANSCEIVER:** 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver dependable 10GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 10GBASE-BX 10Gbps 10G Bi-Directional Downstream Single Mode (SMF) LC Connector 1330nmTx/1270nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **BACKED FOR LIFE:** Backed by a lifetime warranty on the life of the module itself and not the life of your switch; our modules won't void your OEM support and are supported by our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

---

### Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
Industry Standards	IEEE 802.3ae 10GBASE-BX

---

### Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1330nmTx/1270nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	646,156,559 hours
Power Consumption (In Watts)	< 1.3W

---



**Physical  
Characteristics**

Product Length	0.5 in [13.9 mm]
Product Width	2.3 in [58.4 mm]
Product Height	0.5 in [12.6 mm]
Weight of Product	0.8 oz [24.0 g]

---

**Packaging  
Information**

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90.0 mm]
Package Height	1.2 in [31.0 mm]
Shipping (Package) Weight	1.8 oz [50.0 g]

---

**What's in the  
Box**

Included in Package	SFP+ Transceiver
---------------------	------------------

---

***\*Product appearance and specifications are subject to change without notice.***

