

MSA Uncoded SFP+ Transceiver Module - 10GBASE-BX - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (SFP-10GB-BX-U-20-ST)

Product ID: SFP-10GB-BX-U-20-ST



The SFP-10GB-BX-U-20-ST is a MSA Compliant upstream fiber SFP transceiver which pairs with StarTech.com's SFP-10GB-BX-D-20-ST. They are designed, programmed and tested to work with 10GBase-BX compatible MSA switches and routers. The SFP+ transceiver module supports a maximum distance of up to 20 km (12.4 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 1270nmTx/1330nmRx
- Maximum Data Transfer Rate: 10Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 20 km (12.4 mi)
- Power Consumption: Low power consumption
- DDM: Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP+ modules and direct-attach SFP+ Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **MSA UNCODED SFP+ TRANSCEIVER:** 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver dependable 10GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two.
- **TECHNICAL SPECS:** 10GBASE-BX 10Gbps 10G Bi-Directional Upstream Single Mode (SMF) LC Connector 1270nmTx/1330nmRx Digital Diagnostic Monitoring (DDM) Distances up to 20km (12.4mi).
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself and not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- Hot-swappable with fiber-optic modules

Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
Industry Standards	IEEE 802.3ae 10GBASE-BX

Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	20 km (12.4 mi)
Type	Single Mode
Wavelength	1270nmTx/1330nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	646,156,559 hours

Connector(s)

Connector A	SFP Slot
Connector B	Fiber Optic LC Duplex

Physical Characteristics

Product Length	0.5 in [13.9 mm]
Product Width	2.3 in [58.4 mm]
Product Height	0.5 in [12.6 mm]
Weight of Product	0.8 oz [24 g]

Packaging Information

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90 mm]
Package Height	1.2 in [31 mm]
Shipping (Package) Weight	1.8 oz [50 g]

What's in the Box

Included in Package	SFP+ Transceiver
---------------------	------------------

****Product appearance and specifications are subject to change without notice.***

