

MSA Uncoded SFP+ Module - 10GBASE-SR - 10GbE Multi Mode Fiber (MMF) Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 300m - 850nm - DDM

Product ID: SFP-10GBASE-SR-ST



The SFP-10GBASE-SR-ST is an 10 GMSA compliant fiber SFP+ transceiver that's designed, programmed and tested to work with 10GBase-SR compatible MSA switches and routers. The SFP+ transceiver module supports a maximum distance of up to 300 m (984 ft) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 850nm
- Maximum Data Transfer Rate: 10 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 300 m (984 ft)
- MTBF: 646,156,559 hours
- Power Consumption: < 1.3 W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP+ modules and direct-attach SFP+ cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% MSA UNCODED SFP+ TRANSCEIVER:** Designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver dependable 10GbE connectivity
- **TECHNICAL SPECS:** 10GBASE-SR 10Gbps Multi Mode (MMF) LC Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 300m (984ft)
- **TESTED FOR COMPATIBILITY:** Hot-swappable in MSA Compliant routers and switches; DDM support reports the transceiver's status to most SNMP network management tools.
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself and not the life of your switch; our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
Industry Standards	IEEE 802.3ae 10GBASE-SR

Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	300 m (984 ft)
Type	Multi Mode
Wavelength	850nm
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	646,156,559 hours
Power Consumption (In	< 1.3W

Watts)

**Physical
Characteristics**

Product Length	0.5 in [13.9 mm]
Product Width	2.3 in [58.4 mm]
Product Height	0.5 in [13.7 mm]
Weight of Product	0.7 oz [20 g]

**Packaging
Information**

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90 mm]
Package Height	1.2 in [31 mm]
Shipping (Package) Weight	1.8 oz [50 g]

**What's in the
Box**

Included in Package	SFP+ Transceiver
---------------------	------------------

****Product appearance and specifications are subject to change without notice.***

