

MSA Uncoded SFP Module - 1000BASE-TX - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP
- RJ-45 100m

Product ID: SFP1000TXST



The SFP1000TXST is an MSA compliant copper SFP transceiver that's designed, programmed and tested to work with 1000BASE-TX compatible MSA switches and routers. The SFP transceiver module supports a maximum distance of up to 100 m (328 ft) and delivers dependable 1 GbE connectivity over copper cabling. **Technical Specifications:**

- Maximum Data Transfer Rate: 1000 Mbps
- Type: Copper
- Connection Type: RJ45 Connector
- Maximum Transfer Distance: 100 m (328 ft)
- Power Consumption: Less than 1.3 Watt
- DDM: No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

- Replace defective or damaged SFP modules
- Expand your network to remote segments

Features

- **TESTED FOR COMPATIBILITY:** Hot-swappable in MSA Compliant routers and switches
- **WORKS WITH MSA COMPLIANT SWITCHES:** Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- Uses a cost-effective cabling alternative to fiber-optic set ups
- **100% MSA UNCODED SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver dependable 1GbE connectivity
- **TECHNICAL SPECS:** 1000BASE-TX 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself and not the life of your switch; our modules won't void your OEM warranty and supported by our Tech Advisors 5/24

Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
Industry Standards	IEEE 802.3z 1000BASE-TX

Performance

Maximum Data Transfer Rate	1000 Mbps
Max Transfer Distance	100 m (328 ft)
Type	Copper
Fiber Operating Mode	Full-Duplex
DDM	No
Compatible Networks	1000 Mbps (1 Gbps)
Power Consumption (In Watts)	< 1.3 W

Connector(s)

Local Unit Connectors	RJ-45
-----------------------	-------

Special Notes / Requirements

Note	For use in 1 Gigabit networking equipment and media converters
------	--

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

Physical Characteristics

Product Length	2.3 in [58.4 mm]
Product Width	0.5 in [13.9 mm]
Product Height	0.5 in [12.6 mm]
Weight of Product	0.9 oz [25.0 g]

Packaging Information

Package Length	4.7 in [12.0 cm]
Package Width	3.5 in [90.0 mm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	1.8 oz [52.0 g]

What's in the Box

Included in Package	SFP transceiver
---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***

