

Dell EMC SFP-10G-BX40-D Compatible SFP+ Module - 10GBASE-BX-D - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (SFP10GBX40DS)

**Product ID:** SFP10GBX40DS



The SFP10GBX40DS is a Dell EMC SFP-10G-BX40-D compatible downstream fiber SFP transceiver which pairs with StarTech.com's SFP10GBX40US. They are designed, programmed and tested to work with 10GBase-BX40 compatible Dell EMC switches and routers. The SFP+ transceiver module supports a maximum distance of up to 40 km (24.8 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 1270nmTx/1330nmRx
- Maximum Data Transfer Rate: 10Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 40 km (24.8 mi)
- MTBF: 3,736,187 hours
- Power Consumption: < 1.6W
- DDM: Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

### Features

- **100% DELL EMC SFP-10G-BX40-D COMPATIBLE:** 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ designed, programmed and tested to work with compatible Dell EMC switches and routers to deliver dependable 10GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 10GBASE-BX-D 10Gbps 10G Bi-Directional Downstream Single Mode (SMF) LC Connector 1330nmTx/1270nmRx Digital Diagnostic Monitoring (DDM) Distances up to 40km (24.8mi)
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with Dell EMC routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools

---

#### Hardware

Warranty	Lifetime
Compatible Brand	Dell EMC
Industry Standards	IEEE 802.3 10GBASE-BX40

---

#### Performance

Maximum Data Transfer Rate	10.31 Gbps
Max Transfer Distance	40 km (24.8 mi)
Type	Single Mode
Wavelength	1270nmTx/1330nmRx 1270nmTx/1330nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps



MTBF 3,736,187 hours

Power Consumption (In  
Watts) < 1.6W

---

**Physical  
Characteristics**

Product Length 0.5 in [13.9 mm]

Product Width 2.3 in [58.4 mm]

Product Height 0.5 in [12.6 mm]

Weight of Product 1.1 oz [30 g]

---

**Packaging  
Information**

Package Length 4.5 in [11.5 cm]

Package Width 3.5 in [90 mm]

Package Height 1.2 in [31 mm]

Shipping (Package)  
Weight 1.8 oz [50 g]

---

**What's in the  
Box**

Included in Package SFP+ Transceiver

---

*\*Product appearance and specifications are subject to change without notice.*

