

Cisco SFP-10G-SR-X Compatible SFP+ Module - 10GBASE-SR - 10GbE Multimode Fiber MMF Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 300m - 850nm - DDM Cisco Firepower, ASR9000, C9300

Product ID: SFP10GSRXST



The SFP10GSRXST is a Cisco SFP-10G-SR-X compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 10GbE connectivity over fiber cable, for 10GBASE-SR compliant networks, with a maximum distance of up to 300 m (984 ft.).

 850 nm 10Gbps Multimode Fiber LC Connector 300 m (984 ft.) 1,967,709 hours Less than 1.2 Watts Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Expand your network to remote segments
- Replacing defective or damaged SFP modules in Juniper switches and routers

Features

- **100% CISCO SFP-10G-SR-X COMPATIBLE:** Works with Cisco switches like Firepower, ASR9000, C9300, C3850, C9500 and others
- **TECHNICAL SPECS:** 10GBASE-SR 10 Gbps Multi Mode (MMF) LC Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 300m (984ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware	Warranty	Lifetime
	Compatible Brand	Cisco
	WDM	No
	Industry Standards	IEEE 802.3ae 10GBASE-SR
Performance	Maximum Data Transfer Rate	10 Gbps
	Max Transfer Distance	300 m (984 ft)
	Type	Multi Mode
	Wavelength	850nm
	Fiber Operating Mode	Full-Duplex
	DDM	Yes
	Compatible Networks	10 Gbps
	MTBF	1,967,709 hours
	Power Consumption (In Watts)	< 1.3 W
	Connector(s)	Local Unit Connectors
Special Notes / Requirements	Note	For use in 10 Gigabit fiber networking equipment and media converters
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 185F)
	Humidity	5~95% RH
Physical Characteristics	Product Length	2.3 in [58.400 mm]
	Product Width	0.5 in [13.900 mm]
	Product Height	0.5 in [12.600 mm]

	Weight of Product	0.8 oz [22.000 g]
Packaging Information	Package Length	3.7 in [93.000 mm]
	Package Width	4.7 in [1.2 cm]
	Package Height	1.3 in [32.000 mm]
	Shipping (Package) Weight	1.8 oz [50.000 g]
What's in the Box	Included in Package	SFP+ transceiver

**Product appearance and specifications are subject to change without notice.*

