

Juniper SFP-1FE-FX Compatible SFP Module - 100BASE-FX - 100MbE Multimode Fiber MMF Optic Transceiver - 100Mb Ethernet SFP - LC 2km - 1310nm - DDM

**Product ID:** SFP1FEFXST



The SFP1FEFXST is a Juniper SFP-1G-ZC compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 100 Mbps connectivity over fiber cable, for 100Base-FX compliant networks, with a maximum distance of up to 80 km (49.7 mi).

Technical Specifications:

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 100 Mbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 2 km (1.2 mi)
- MTBF: 1,472,572 hours
- Power Consumption: Low power consumption
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

### Features

- **100% JUNIPER SFP-1FE-FX COMPATIBLE SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 100MbE connectivity
- **TECHNICAL SPECS:** 100BASE-FX 100 Mbps Multi Mode (MMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 2km (1.2mi)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Juniper routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

---

#### Hardware

Warranty	3 Years
Compatible Brand	Juniper
Industry Standards	IEEE 802.3 100BASE-FX

---

#### Performance

Maximum Data Transfer Rate	100 Mbps
Max Transfer Distance	2 km (1.2 mi)
Type	Multi Mode
Wavelength	1310nm
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	100 Mbps
MTBF	1,472,572 hours

---

**Connector(s)**

Connector A	SFP Slot
Connector B	Fiber Optic LC Duplex

---

**Physical Characteristics**

Product Length	2.6 in [65.0 mm]
Product Width	0.6 in [14.0 mm]
Product Height	0.5 in [12.0 mm]
Weight of Product	2.5 oz [72.0 g]

---

**Packaging Information**

Package Length	9.1 in [23.0 cm]
Package Width	8.1 in [20.7 cm]
Package Height	0.6 in [15.0 mm]
Shipping (Package) Weight	2.8 oz [80.0 g]

---

**What's in the Box**

Included in Package	SFP Transceiver
---------------------	-----------------

---

***\*Product appearance and specifications are subject to change without notice.***

