

Juniper SFP-1GE-FE-E-T Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m

**Product ID:** SFP1GEFEETST



The SFP1GEFEETST is a Juniper SFP-1GE-FE-E-T compatible copper transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over copper cable, for 10/100/1000Base-T compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Copper
- Connection Type: RJ-45
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 4,655,371 hours
- Power Consumption: Low power consumption
- Digital Diagnostics Monitoring (DDM): No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

## Applications

## Features

- **100% JUNIPER SFP-1GE-FE-E-T COMPATIBLE SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **TECHNICAL SPECS:** 1000BASE-T 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Juniper routers and switches
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

---

### Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com Juniper SFP-1GE-FE-E-T Compatible SFP Transceiver - 1GbE 100m

---

### Automation Inputs

Brand Compatible SFP without trade mark	Juniper
---	---------

---

### Hardware

Compatible Brand	Juniper
Industry Standards	IEEE 802.3 10/100/1000BASE-T

---

### Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	100 m (328 ft)
Type	Copper
Fiber Operating Mode	Full-Duplex
DDM	No
Compatible Networks	1000 Mbps (1 Gbps)



MTBF 4,655,371 hours

---

**Physical  
Characteristics**

Product Length	2.6 in [65.0 mm]
Product Width	0.6 in [14 mm]
Product Height	0.5 in [12 mm]
Weight of Product	2.5 oz [72 g]

---

**Packaging  
Information**

Package Length	9.1 in [23 cm]
Package Width	8.1 in [20.7 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	2.8 oz [80 g]

---

**What's in the  
Box**

Included in Package	SFP Transceiver
---------------------	-----------------

---

***\*Product appearance and specifications are subject to change without notice.***

