

Cisco SFP-H10GB-CU5M Compatible 5m 10G SFP+ to SFP+ Direct Attach Cable Twinax - 10GbE SFP+ Copper DAC 10 Gbps Low Power Passive Mini GBIC/Transceiver Module DAC Firepower ASR920 ASR9000

Product ID: SFPCMM5M



The SFPCMM5M is a Cisco compatible direct-attach copper SFP+ cable that's designed, programmed and tested to work with Cisco brand compatible switches and routers and complies with MSA industry standards.

This passive Twinax copper cable supports 10 Gigabit Ethernet applications connected through SFP+ (Mini-GBIC) ports. This copper SFP+ cable is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

Designed for high-speed performance, this low-power, low-latency SFP+ cable is a cost-effective alternative to fiber-optic cable assemblies, supporting short-distance applications such as point-to-point in-rack network switch or server connections.

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

- Use in 10Gb Ethernet and Fiber Channel applications
- Point-to-point in-rack and across rack network switch/server connections (Storage Area Networks (SAN), Network Attached Storage (NAS), Storage Servers, etc.)

Features

- **100% CISCO SFP-H10GB-CU5M COMPATIBLE:** Works with Cisco switches like Firepower, ASR920, ASR9000, C9300, C3850 and others
- **TECHNICAL SPECS:** 5m (16.4ft) 10 Gbps Passive Twinax (Copper) 2x SFP+ Pluggable Connector 100 Ohm Impedance 30 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM support and with access to our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Low power 10GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers

Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Impedance	100 Ohm
Compatible Networks	10 Gbps
Power Consumption (In Watts)	< 0.5 W

Connector(s)

Connector A	SFP+
Connector B	SFP+

Environmental

Operating Temperature	0°C to 70°C
Storage Temperature	-40°C to 80°C

Physical Characteristics

Product Length	16.4 ft [5.0 m]
Product Width	0.6 in [14.0 mm]
Product Height	0.5 in [12.0 mm]



Weight of Product	11.0 oz [311.0 g]
-------------------	-------------------

Packaging Information

Package Length	13.0 in [33.0 cm]
----------------	-------------------

Package Width	10.0 in [25.5 cm]
---------------	-------------------

Package Height	0.8 in [20.0 mm]
----------------	------------------

Shipping (Package) Weight	11.6 oz [328.0 g]
---------------------------	-------------------

What's in the Box

Included in Package	5m SFP+ 10-Gigabit Ethernet (10GbE) Twinax Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***

