

## Cisco Compatible Gigabit Fiber SFP Transceiver Module SM LC w/ DDM – 40 km (Mini-GBIC)

Produkt ID: SFPG1340C



The SFPG1340C Cisco® Compatible Gigabit Fiber SFP Transceiver Module SM LC – 40 km (24.8 miles) is built to comply with MSA (Multi-Sourcing Agreement) standards to offer a cost-effective way to add, replace or upgrade a Single-Mode LC port on your Gigabit fiber networking equipment or fiber media converter.

Supporting data rates up to 1.25 Gbps as well as Digital Diagnostics Monitoring (DDM), this LC SFP/Mini-GBIC module can be installed into any fiber networking device with an MSA or Cisco compliant SFP port. Delivering both convenience and scalability, this fiber transceiver is fully hot-pluggable, which enables you to install the module without interrupting network traffic or requiring a device reboot.

This 1310nm single-mode SFP module is compatible with the Cisco GLC-EX-SMD transceiver.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifikat, rapporter och kompatibilitet

#### Användning

- Replacing defective or damaged SFPs/Mini GBICs in MSA or Cisco compliant equipment
- Expand your Gigabit network to remote segments

#### Funktioner

- Data rates up to 1.25 Gbps
- Supports distances up to 40 km (24.8 miles)
- Complies with SFP Multi-Source Agreements standards (MSA)
- Compatible with Cisco equipment
- LC Fiber connector
- Fully Hot Pluggable

---

#### Hårdvara

Garantipolicy	3 Years
WDM	Nej
Industristandarder	IEEE 802.3z 1000BASE-EX

---

#### Prestanda

Maximal dataöverföringshastighet	1.25 Gbps
Maximalt överföringsavstånd	40 km (24.8 mi)
Fibertyp	Enkelläge
Våglängd	1310nm
Fiber-driftsläge	Halv/full-duplex
DDM	Ja
Kompatibla nätverk	1000 Mbps (1 Gbps)

---

#### Kontakt(er)

Lokala enhetskontakter Fiberoptisk LC duplex

---

#### Särskilda anmärkningar/krav

Obs. For use in Gigabit fiber networking equipment and media converters

---

Miljö

Drifttemperatur	0°C to 70°C (32°F to 158°F)
Förvaringstemperatur	-40°C to 85°C (-40°F to 185°F)
Luftfuktighet	30~70% RH

---

Utseende

Produktlängd	2.4 in [60.0 mm]
Produktbredd	0.5 in [12.0 mm]
Produkt höjd	0.4 in [10.0 mm]
Produktvikt	0.6 oz [17.0 g]

---

Förpackning

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90.0 mm]
Package Height	1.2 in [30.0 mm]
Fraktvikt (förpackning)	1.7 oz [49.0 g]

---

Vad det är i lådan

Ingår i paketet	1.25 Gbps Single Mode LC SFP
-----------------	------------------------------

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

