

Juniper SFP-GE10KT13R15 Compatible SFP Module - 1000BASE-BX-U - 1GbE Gigabit Ethernet BiDi Fiber (SMF) (SFPGE10KT3R5)

**Product ID:** SFPGE10KT3R5



The SFPGE10KT3R5 is a Juniper SFP-GE10KT3R5 compatible fiber transceiver module that has been designed, programmed, and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000Base-BX10-U compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- Wavelength: 1310nmTx/1550nmRx
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 3,713,222 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

### Features

- **100% JUNIPER SFP-GE10KT13R15 COMPATIBLE:** 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 1000BASE-BX-U 1Gbps 10G Bi-Directional Upstream Single Mode (SMF) LC Connector 1310nmTx/1550nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with Juniper routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools

---

#### Hardware

Warranty	3 Years
Compatible Brand	Juniper
Industry Standards	IEEE 802.3 1000BASE-BX10-U

---

#### Performance

Maximum Data Transfer Rate	1.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nmTx/1550nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	3,713,222 hours



Power Consumption (In Watts) < 1.3W

---

**Connector(s)**

Connector A	SFP Slot
Connector B	Fiber Optic LC Simplex

---

**Physical Characteristics**

Product Length	2.6 in [65.0 mm]
Product Width	0.6 in [14.0 mm]
Product Height	0.5 in [12.0 mm]
Weight of Product	2.5 oz [72.0 g]

---

**Packaging Information**

Package Length	9.1 in [23.0 cm]
Package Width	8.1 in [20.7 cm]
Package Height	0.6 in [15.0 mm]
Shipping (Package) Weight	2.8 oz [80.0 g]

---

**What's in the Box**

Included in Package	SFP Transceiver
---------------------	-----------------

---

*\*Product appearance and specifications are subject to change without notice.*

