

Juniper SFP-GE10KT15R13 Compatible SFP Module - 1000BASE-BX-D - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (SFPGE10KT5R3)

Product ID: SFPGE10KT5R3



The SFPGE10KT5R3 is a Juniper SFPP-10GE-LR compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000Base-BX10-D compliant networks, with a maximum distance of up to 40 km (24.8 mi).

Technical Specifications:

- Wavelength: 1550nmTx/1310nmRx
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single-Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 3,713,222 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% JUNIPER SFP-GE10KT15R13 COMPATIBLE:** 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 1000BASE-BX-D 1Gbps 10G Bi-Directional Downstream Single Mode (SMF) LC Connector 1310nmTx/1550nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with Juniper routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools

Hardware

Warranty	3 Years
Compatible Brand	Juniper
Industry Standards	IEEE 802.3 1000BASE-BX10-D

Performance

Maximum Data Transfer Rate	1.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1550nmTx/1310nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	3,713,222 hours

Power Consumption (In Watts) < 1.3W

Connector(s)

Connector A	SFP Slot
Connector B	Fiber Optic LC Duplex

Physical Characteristics

Product Length	2.6 in [65.0 mm]
Product Width	0.6 in [14.0 mm]
Product Height	0.5 in [12.0 mm]
Weight of Product	2.5 oz [72.0 g]

Packaging Information

Package Length	9.1 in [23.0 cm]
Package Width	8.1 in [20.7 cm]
Package Height	0.6 in [15.0 mm]
Shipping (Package) Weight	2.8 oz [80.0 g]

What's in the Box

Included in Package	SFP Transceiver
---------------------	-----------------

**Product appearance and specifications are subject to change without notice.*

