

Cisco GLC-SX-MM Compatible SFP Module - 1000BASE-SX - 1GbE Multimode Fiber MMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 550m - 850nm - Cisco IE3400, IE3300, IE3200
Product ID: SFPGLCSXMMST



The SFPGLCSXMMST is a Cisco GLC-SX-MM compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1GbE (1000 Mbps) connectivity over fiber cable, for 1000BASE-SX compliant networks, with a maximum distance of up to 550 m (1804 ft).

 850 nm 1.25 Gbps Multi Mode Fiber LC Connector 550 m (1804 ft) 3,092,408 hours Less than 1 Watt No

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

Features

- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Cisco routers and switches
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the module itself, not your equipment; our modules won't void your OEM support and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- **100% CISCO GLC-SX-MM COMPATIBLE:** Works with Cisco switches like IE3400, IE3300, IE3200, ME1200, ME2400 and others
- **TECHNICAL SPECS:** 1000BASE-SX 1 Gbps Multi Mode (MMF) LC Connector 850nm Distances up to 550m (1804ft)

Hardware	Warranty	Lifetime
	Compatible Brand	Cisco
	WDM	No
	Industry Standards	IEEE 802.3z 1000BASE-SX
Performance	Maximum Data Transfer Rate	1.25 Gbps
	Max Transfer Distance	550 m (1804 ft)
	Type	Multi Mode
	Wavelength	850nm
	Fiber Operating Mode	Half/Full-Duplex
	DDM	No
	Compatible Networks	1000 Mbps (1 Gbps)
	MTBF	3,381,761 hours
	Power Consumption (In Watts)	< 1 W
	Connector(s)	Local Unit Connectors
Special Notes / Requirements	Note	For use in Gigabit fiber networking equipment and media converters
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 85F)
	Humidity	30~70% RH
Physical Characteristics	Product Length	2.4 in [60.000 mm]
	Product Width	0.5 in [12.000 mm]
	Product Height	0.4 in [10.000 mm]
	Weight of Product	0.6 oz [16.000 g]

Packaging Information	Package Length	4.6 in [1.2 cm]
	Package Width	3.7 in [95.000 mm]
	Package Height	1.3 in [32.000 mm]
	Shipping (Package) Weight	3.4 oz [95.000 g]

What's in the Box	Included in Package	1.25 Gbps Multimode LC SFP
--------------------------	---------------------	----------------------------

****Product appearance and specifications are subject to change without notice.***

