

MSA Uncoded SFP Module - 1000BASE-SX - 1GbE Multi Mode Fiber (MMF) Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 550m - 850nm - DDM - TAA

Produkt ID: SFPSXMM



The SFPSXMM is a TAA compliant MSA compliant fiber SFP transceiver that's designed, programmed and tested to work with 1000BASE-SX compatible MSA switches and routers. The SFP transceiver module supports a maximum distance of up to 550 m (1804 ft) and delivers dependable 10 GbE connectivity over fiber cabling. **Technical Specifications:**

- Wavelength: 850 nm
- Maximum Data Transfer Rate: 1.25 Gbps
- Type: Multi Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 550 m (1804 ft)
- MTBF: 78,286 hours
- Power Consumption: Less than 1 Watt
- DDM: No

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifikat, rapporter och kompatibilitet



Användning

- Replace defective or damaged SFP modules
- Utvidga nätverket till avlägsna platser

Funktioner

- 100% MSA UNCODED SFP TRANSCEIVER: Designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver reliable 1GbE connectivity
- TECHNICAL SPECS: 1000BASE-SX | 1Gbps | Multi Mode (MMF) | LC Connector | 850nm | Digital Diagnostic Monitoring (DDM) | Distances up to 550m (1804ft)
- TESTED FOR COMPATIBILITY: Hot-swappable in MSA Compliant routers and switches
- WORKS WITH MSA COMPLIANT SWITCHES: Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- Kan hotswappas med fiberoptiska moduler

Hårdvara

Garantipolicy	2 Years
Compatible Brand	MSA Compliant
Industristandarder	IEEE 802.3z 1000BASE-SX

Prestanda

Maximal dataöverföringshastighet	1.25 Gbps
Maximalt överföringsavstånd	550m [1804ft]
Fibertyp	Multiläge

Våglängd	850nm
Fiber-driftsläge	Full-duplex
DDM	Ja
Kompatibla nätverk	1000 Mbps (1 Gbps)
Medeltid mellan fel (MTBF)	78,286 hours
Strömförbrukning	< 1 W

Kontakt(er)

Lokala enhetskontakter 1 - Fiberoptisk LC duplex

Ström

Utpänning 3.3V DC

Miljö

Drifttemperatur	0°C to 70°C (32°F to 158°F)
Förvaringstemperatur	-40°C to 85°C (-40°F to 85°F)
Luftfuktighet	5 till 95 % RH

Utseende

Produktlängd	2.2 in [55.0 mm]
Produktbredd	0.5 in [1.3 cm]
Produkthöjd	0.4 in [0.9 cm]
Produktvikt	0.6 oz [18.0 g]

Förpackning

Paketets längd	4.4 in [11.3 cm]
Paketets bredd	2.6 in [6.5 cm]
Paketets höjd	1.1 in [2.7 cm]
Fraktvikt (förpackning)	1.4 oz [40.0 g]

Vad det är i lådan

Ingår i paketet

1 - SFP Multimode LC Transceiver

Warranty
Information

Warranty

2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.