

Sit-Stand Monitor Arm with Keyboard/Mouse Tray - Adjustable Desk Mount Sit-Stand Workstation Arm for Single 27" VESA Display - Ergonomic Articulating Standing Desk Converter - TAA

Produkt-ID: SIT-STAND-ARM-1MS



This sit-stand monitor arm transforms your desk or tabletop into an ergonomic workstation. The monitor arm features a keyboard tray and easy height adjustment that lets you alternate between sitting and standing, without interrupting your workflow. Move your workstation up or down, left or right, to meet your needs.

Adjust your position, with one smooth motion. Simply lift the work surface up to 17.7" (450 mm), to elevate both your monitor and keyboard. You can adjust the tension to your own preference. The monitor mount has a separate height adjustment of up to 4.9" (124 mm) along the column.

This sit-stand monitor arm supports one monitor up to 27" (or 34" ultrawide). The swing arm swivels +/-90° and tilts +35°/-5° for ideal viewing. The VESA mount also rotates up to 360° for portrait or landscape orientation.

The monitor arm features a large keyboard tray (17.68 x 8.15" / 449 x 207 mm) with ample working space. A slide-out tray (8.5 x 8.4" / 217 x 213 mm) holds your mouse, on the left or right.

To make the most of your workspace, you can tuck the monitor arm away when it's not in use, to free up space. The keyboard tray also folds up to 90°.

The compact sit-stand monitor arm features grommet or desk-clamp installation and fits easily into your workspace, including space-limited corners.

This sit stand converter is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **SIT-TO-STAND DESK ARM:** Convert your existing desk or table to a sit-stand ergonomic workstation with adjustable height, swivel, and extension - VESA compatible (75x75/100x100 mm) - Supports up to 27" (or 34" ultrawide) monitor and 17.6lb/8kg
- **FULLY ADJUSTABLE:** Standing desk converter w/ spring-assisted height adjustment & +/-90 swivel base is designed for max stability & flexible installation (desk-clamp or grommet) in space-limited areas
- **WIDE RANGE OF MOTION:** The articulating ergonomic single monitor arm supports +35/-5° tilt, 360° rotating computer screens (landscape/portrait) & adjustable height along the 4.9" (124mm) track - Black version: ARMSTSCP1
- **MAXIMIZE DESK SPACE:** This desk mount stand-up workstation has a padded keyboard tray with slide-out right/left mouse tray that folds up 90° when not in use & cable management for a minimal footprint - Add CPUWALLMNT (sold separately) to mount a PC nearby
- **EINFACHE REINIGUNG:** Die abnehmbare Mausablage und die ergonomische Handgelenkstützenabdeckung ermöglichen die häufige Reinigung aller stark beanspruchten Oberflächen für einen hygienischen gemeinsam genutzten Sitz-/Steharbeitsplatz mit Desktop Monitor

Hardware

Garantiebestimmungen 2 Years

Wandmontierbar Nein

Kabelmanagement Ja

Inklusive Werkzeuge Ja

Gelenk Ja

Anzahl der unterstützten Displays 1

Montageoptionen Schreibtisch- & Kabeldurchführungsklemme

	VESA-Lochmuster	75x75 mm
		100x100 mm
Stärke der Montageoberfläche		Schreibtischklemme: Tischdicke 8-50 mm
		Tüllenklemme: Tischdicke 8-50 mm
		Tischöffnung für Kabeldurchführungsklemme: 8,5-65 mm
Leistung		
	Allgemeine Spezifikationen	Tragkraft des Monitorarm: 8 kg Tragkraft der Tastaturablage bei Montage mit Tüllenklemme: 2,5 kg Tragkraft der Tastaturablage mit Schreibtischklemme: 1,5 kg
	Gewichtskapazität	17.6 lb [8 kg]
	Weight Capacity of Keyboard Tray	5.5 lb [2.5 kg]
	Maximale Bildschirmgröße	27"
	Fits UltraWide Displays	Ja
	Höhenverstellung	Ja
	Minimale Höhe	15.6 in [396 mm]
	Maximale Höhe	36.5 in [926 mm]
	Maximale Armlänge	21.6 in [548 mm]
	Neigung	+35° / -5°
	Keyboard Tray Tilt	0 to 90°
	Schwenkung/Drehung	+90° / -90°
	Displayrotation	360°
	Diebstahlsicherung	Nein

Physische Eigenschaften

Farbe	Silber & Weiß
Gehäusetyt	Steel, Aluminum and Plastic
Keyboard Tray Width	17.7 in [449 mm]
Keyboard Tray Depth	8.1 in [207 mm]
Produktlänge	37.0 in [94.0 cm]
Produktbreite	35.0 in [89.0 cm]
Produkthöhe	30.4 in [77.3 cm]
Produktgewicht	25.2 lb [11.4 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	16.5 in [41.8 cm]
Paketbreite	35.4 in [89.8 cm]
Pakethöhe	8.6 in [21.8 cm]
Versandgewicht (Verpackung)	30.6 lb [13.9 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Monitorarm
	1 - Tastaturablage
	1 - Säule
	1 - VESA-Monitorbefestigung
	1 - Basis
	2 - Adhesive Strips
	1 - Tastaturablagefach Abdeckung
	1 - Klemme L-Bügel
	1 - Klemme Schraubensatz

- 1 - Basis-Pad
- 4 - Klemmschrauben
- 1 - Grundplatte
- 1 - Durchführungsplatte
- 1 - Steckschlüssel
- 1 - Metall-Unterlegscheibe
- 1 - Kunststoff-Unterlegscheibe
- 4 - Schrauben für Basis
- 2 - M6x25mm Schrauben
- 1 - M8x65mm Screws
- 4 - Schrauben M6x12 mm
- 4 - Schrauben M4x10 mm
- 3 - M6x10mm Screws
- 1 - M6x8mm Schrauben
- 1 - M8x20mm Schrauben
- 2 - M3x8mm Screw
- 1 - 2.5mm Hex Key
- 1 - Sechskantschlüssel, 5 mm
- 1 - Sechskantschlüssel, 6 mm
- 1 - Benutzerhandbuch

Garantieinformationen

Warranty

2 Jahre

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.