

Fiber Optic Cable - Single-Mode Duplex 9/125 - LSZH - LC/LC - 1 m

Produkt ID: SMFIBLCLC1



The SMFIBLCLC1 1m LC to LC Single-Mode Duplex Fiber Cable features 9/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex single-mode applications.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire – an ideal solution for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 9/125 (OS1) Single-Mode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability, and is backed by our lifetime warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Use in Gigabit Ethernet and Fiber Channel applications
- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication/Data communication
- Fiber Connections in Patch Panels, Hubs, Switches, Routers

## Funktioner

- 2x LC SM male connectors
- OS1 (9/125)
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards
- Molded connectors

---

### Hårdvara

Garantipolicy	Lifetime
Brandteknisk klass	LSZH-klassad (Low Smoke Zero Halogen)
Fiberstorlek	9/125

---

### Prestanda

Maximal dataöverföringshastighet	100Gbps
Kabelklassificering	10Gbps / 40Gbps / 100Gbps
Fiberklassificering	OS1
Fibertyp	Enkelläge

---

### Kontakt(er)

Connector A	Fiberoptisk LC duplex
Connector B	Fiberoptisk LC duplex

---

### Miljö

Drifttemperatur	-20°C to 60°C (-4°F to 140°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~90% RH

---

### Utseende



Färg	Gul
Kabellängd	39.4 in [100 cm]
Produktlängd	39.4 in [100.0 cm]
Produktbredd	0.0 in [0.0 mm]
Produkthöjd	0.0 in [0.0 mm]
Produktvikt	0.7 oz [19.0 g]

---

#### Förpackning

Förpackningsantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.6 in [14.0 mm]
Fraktvikt (förpackning)	1.0 oz [28.0 g]

---

#### Vad det är i lådan

Ingår i paketet	1m Single Mode Duplex Fiber Patch Cable LC-LC
-----------------	---

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

