

1 Port PCI 10/100 Mbps Ethernet Network Adapter Card

Produkt ID: ST100S



This 1 Port PCI Fast Ethernet Network Adapter Card offers a reliable, cost-effective Ethernet network connection. Delivering a simple connection to 10/100Mbps Ethernet networks, the NIC features auto-negotiation that senses speed and duplex capabilities of connected devices and full duplex support for data transfer rates up to 200Mbps.

A versatile network interface solution, the NIC is supported by all popular operating systems including Windows, Linux, Mac OS and Novell platforms, and is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet

Användning

- Replacement Ethernet card for a home or office desktop computer
- Adding Ethernet network connectivity for broadband Internet access to an old desktop computer
- Adding a second or redundant network connection for a workstation or server

Funktioner

- Single 10/100Mbps RJ45 Ethernet port
- Compliant with IEEE802.3 CSMA/CD, 802.3 10Base-T and 100Base-TX standards
- Full and Half duplex mode support

- Link speed and duplex mode auto-negotiation
- Link/Activity and 10/100Mbps LED indicators
- Early interrupt on transmit support
- Includes a low profile installation bracket

Hårdvara

Garantipolicy	Lifetime
Portar	1
Gränssnitt	RJ45 (10/100 Ethernet)
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil (inkl. LP-fäste)
Industristandarder	IEEE 802.3/802.3u
Chipset-ID	Realtek - RTL8100C

Prestanda

Maximal dataöverföringshastighet	200 Mbits/Sec
Kompatibla nätverk	10/100 Mbps
Stöd för full-duplex	Ja

Kontakt(er)

Kontakttyp(er)	PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Externa portar	RJ-45

Mjukvara

OS-kompatibilitet	Windows® NT, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11 Windows Server® 2008 R2, 2012, 2016, 2019 Mac OS® 10.0.4, 9.1 / 9.0 Unix, Linux 2.6 to 4.11.x <i>LTS Versions Only</i>
-------------------	---



NetWare 3.x/4.x

Särskilda
anmärkningar/krav

Obs.	IRQ and I/O Address assigned by system
------	--

Indikatorer

LED-indikatorer	10/100Mbps selection Network link/activity
-----------------	---

Ström

Strömförbrukning	≤1.5W
------------------	-------

Miljö

Drifttemperatur	0°C to 55°C (32°F to 131°F)
Luftfuktighet	10~90% RH Non-condensing

Utseende

Produktlängd	4.7 in [12.0 cm]
Produktbredd	1.3 in [32.0 mm]
Produkt höjd	4.7 in [12.0 cm]
Produktvikt	1.4 oz [40.0 g]

Förpackning

Package Length	5.6 in [14.3 cm]
Package Width	6.7 in [17.0 cm]
Package Height	1.1 in [29.0 mm]
Fraktvikt (förpackning)	4.7 oz [133.0 g]

Vad det är i lådan

Ingår i paketet	PCI Ethernet Card Low Profile Bracket Driver CD Instruction Manual
-----------------	---



* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

