

2 Port VGA over Cat5 Video Extender – Transmitter

Produkt ID: ST1212T



The ST1212T 2-Port VGA over Cat 5 Extender is designed for use with our ST121 VGA over Cat 5 extension series, offering convenient video distribution at distances of up to 500 feet (150 meters) using standard Cat 5 (or better) Ethernet cabling.

Comprised of the transmitter unit only, the ST1212T requires one Receiver Unit (ST121R) per display that you are connecting.

For added versatility, the VGA over Cat 5 Repeater (ST121EXT) can be used to extend the distance between the transmitter and receiver by an additional 500 feet (150 meters), for a total extension distance of 1000 feet (300 meters). Similarly, up to 3 repeater units can be used between transmitter and receiver, enabling you to connect monitors at each repeater, while still extending the total distance.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Use a combination of repeaters or receivers, to simplify adding more displays to your digital signage installation

- Position displays where they will be most effective for viewing, but install the system equipment elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational and corporate sectors, to deliver up to date, eye-catching content
- Expand the range of your advertisements in auditoriums, trade-shows and retail environments

Funktioner

- Features 2 local (VGA) output ports, 2 (VGA over Ethernet) output ports for remote connections
- Extends VGA video by up to 500ft (150m)
- Supports cascading multiple transmitter units
- Pure hardware design, with no software or drivers to install
- Compatible with the ST121EXT repeater unit for further extension
- Compatible with the ST121R receiver

Hårdvara

Garantipolicy	3 Years
Portar	2
Kablage	Cat 5 UTP eller bättre
Kedjekoppling	Ja

Prestanda

Maximalt avstånd	150m [492ft]
Stödda upplösningar	1600x1200 @ 150ft(50m)
	1280x1024 @ 300ft(100m)
	1024x768 @ 500ft(150m)

Kontakt(er)

Lokala enhetskontakter	2 - RJ-45
	1 - VGA (15-stifts, High Density D-Sub)

1 - VGA (15-stifts, High Density D-Sub)

Särskilda

anmärkningar/krav

System- och kabelkrav One [Receiver Unit](/product/ST121R) (ST121R) per display that you are connecting

Indikatorer

LED-indikatorer
1 - Power
1 - Active

Ström

Strömkälla AC-adapter medföljer
Inspänning 100 - 240 AC
Inström 0.8A
Utpänning 12V DC
Utström 0.6A
Polaritet på mittpol Positiv
Strömförbrukning 7.2

Miljö

Drifttemperatur 0°C to 40°C (32°F to 104°F)
Förvaringstemperatur -10°C to 60°C (14°F to 140°F)
Luftfuktighet 0~80% RH

Utseende

Färg Svart
Kabinettyp Aluminium
Produktlängd 3.9 in [10.0 cm]
Produktbredd 2.6 in [6.5 cm]
Produkthöjd 0.8 in [2.0 cm]

Produktvikt 6.9 oz [195.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	4.0 in [10.2 cm]
Package Width	8.6 in [21.9 cm]
Paketets höjd	3.8 in [97.0 mm]
Fraktvikt (förpackning)	18.4 oz [522.0 g]

Vad det är i lådan

Ingår i paketet	1 - 2 Port VGA Extender Unit
	1 - Set Rubber Feet
	1 - Universell strömadapter (NA/EU/UK)
	1 - Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.